

20ft (6m) DisplayPort Cable - 2560 x 1440p - DisplayPort to DisplayPort Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Product ID: DISPLPORT20L



The DISPLPORT20L 20-foot DisplayPort Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI or dual link DVI, while supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (2560x1600).

The cable features latching connectors, with support for two-way display connectivity and optional audio support.

Featuring 26 gauge (AWG) pure copper wire, the cable includes Aluminum and Mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

This 20-foot DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

Features

- **HIGH PERFORMANCE CABLE:** This 20ft (6m) DisplayPort to DisplayPort cable supports 2K (2560x1440p) 30Hz,

Full HD (1920x1200p) 60Hz, 10.8 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for precise audio channel timing & 3D Stereo

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 20 ft (6 m) Black DisplayPort v1.0 DP Latching Male to Male 26 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: MST, GTC Lifetime Warranty

Hardware

	Warranty	Lifetime
Number of Conductors	19	
Connector Plating	Nickel	
Cable Jacket Material	PVC - Polyvinyl Chloride	
Cable Shield Material	Aluminum-Mylar Foil with Braid	
Fire Rating	CMG	

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	26 AWG (0.404 mm)
Cable Length	20.0 ft [6.1 m]
Cable OD	0.3 in [8.5 mm]
Product Length	20.0 ft [6.1 m]

Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	15.9 oz [450.0 g]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.7 cm]
Package Width	9.8 in [25.0 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	1.0 lb [0.5 kg]

What's in the Box

Included in Package	1 - 20 ft DisplayPort Cable with Latches - M/M
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

