

35ft (10.5m) DisplayPort Cable - 1920 x 1200p - Displayport to Displayport Cable - DP to DP Cable for Monitor - DP Video/Display Cord - Latching DP Connectors - HDCP & DPCP

Product ID: DISPLPORT35L



The DISPLPORT35L 35-foot DisplayPort cable provides a connection of up to 35ft between a DisplayPort source and a DisplayPort display, supporting resolutions up to 1920x1200, with no loss of signal quality – more than double the typical DisplayPort connection distance limitation of 16ft.

Its 26 gauge (AWG) pure copper wire, and Aluminum and Mylar shielding helps to eliminate EMI and RFI interference, while its small USB-sized latching connectors support two-way display connectivity and optional audio support.

The DISPLPORT35L DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

Certifications, Reports and Compatibility



Applications

- Connecting a DisplayPort display to a PC or alternative DisplayPort source

Features

- **HIGH PERFORMANCE CABLE:** This 35ft (10m) DisplayPort to DisplayPort cable supports Full HD (1920x1200p) 60Hz, (1920x1080p) 60Hz, 6.48 Gbps bandwidth, Multi-Stream Transport (MST), 5.1, 7.1 Audio Channel, GTC for

precise audio channel timing & 3D Stereo

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Latching DP connectors prevent accidental disconnection
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio
- **APPLICATIONS:** Ideal for home/offices/boardrooms/conference rooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100/5100 or R5000 graphic cards; Use with 1080p/UHD/4K monitors, projector or large display
- **SPECS:** 35 ft (10 m) Black DisplayPort v1.0 DP Latching Male to Male 26 AWG PVC cable jacket, ABS connector shell Shield: Al-Mylar foil with Braid Protocols: MST, GTC Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching
Wire Gauge	26 AWG (0.404 mm)
Cable Length	35.0 ft [10.7 m]
Cable OD	0.3 in [8.5 mm]
Product Length	35.0 ft [10.7 m]
Product Width	0.5 in [1.3 cm]

Product Height 0.8 in [2.1 cm]

Weight of Product 1.7 lb [0.8 kg]

Packaging Information

Package Quantity 1

Package Length 8.3 in [21.2 cm]

Package Width 8.6 in [21.8 cm]

Package Height 2.7 in [6.9 cm]

Shipping (Package) Weight 1.7 lb [0.8 kg]

What's in the Box

Included in Package 1 - 35 ft DisplayPort Cable with Latches - M/M

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

