

USB 3.0 Docking Station - Dual Monitor Laptop Docking Station with HDMI & DVI/VGA Video - 6-port USB 3.1 Gen 1 5Gbps Hub, GbE, Audio - Universal Type-A Dock - Windows & Mac

Product ID: DK30ADD



This USB 3.0 docking station for Mac and Windows laptops gives you display flexibility and the ports you need to maximize workstation performance. The cost-effective dual-monitor docking station provides many video output options including HDMI, DVI and VGA (with adapter), and gives you six USB ports for peripherals, including two fast-charge USB ports.

The USB 3.0 dock expands the display capabilities of your Mac or Windows laptop. Set up dual displays by connecting to one HDMI and one DVI monitor. Plus, the laptop docking station includes a DVI to VGA adapter, so you can connect to a legacy VGA monitor.

- 1x HDMI display + 1x DVI display at 2048 x 1152 resolution @ 60Hz
- 1x HDMI display at 2048 x 1152 resolution + 1x VGA display at 1920 x 1200 resolution @ 60Hz

Transform your laptop into a fully capable workstation. This USB 3.0 dock provides six USB 3.0 (Type-A) ports so you can easily connect your keyboard, external drives and other peripherals, from the single USB 3.0 host connection. Two of the USB 3.0 ports are always-on fast-charge ports, adding charge-and-sync flexibility for up to two mobile devices. The docking station also provides a Gigabit Ethernet port plus a 3.5 mm audio headphone port.

DK30ADD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility





Applications

- Connect to a wide range of monitors in businesses and institutions
- Ideal for shared workspaces in hotels, or for short-term hot desk applications
- Add dual video outputs to a laptop, where the video card can't be replaced

Features

- **FULL FEATURE DOCK:** USB 3.0 Type-A dock features dual monitor options with HDMI & DVI video ports, six USB 3.1 Gen 1 5Gbps Type-A ports, gigabit ethernet, audio port & includes a 1m USB-A host cable
- **MULTIPLE DUAL DISPLAY OUTPUTS:** Flexible dual screen display options for mixed monitor connectivity incl. HDMI + DVI or HDMI + VGA (w/ the incl. DVI to VGA Adapter) to support new and existing set ups
- **USB-A LAPTOP COMPATIBILITY:** DisplayLink certified, this USB 3.0 docking station works with laptop brands like HP, Dell, Lenovo, MacBook, Surface Book / Pro 6, and Chromebooks
- **WIDE OPERATING SYSTEM COMPATIBILITY:** This universal laptop docking station fully supports major operating systems like Windows, macOSx, and ChromeOS
- **PLENTY OF USB PORTS:** This USB 3.0 port replicator has a 6-port downstream USB-A hub (5Gbps SuperSpeed) including two always-on BC 1.2 (1.5A) fast-charge ports that charge without a connected computer

Hardware

Warranty	3 Years
4K Support	No
Fast-Charge Port(s)	Yes
Displays Supported	2
Interface	USB 3.2 Gen 1 (5Gbps)
Bus Type	USB 3.2 Gen 1 (5Gbps)
Industry Standards	USB Battery Charging Specification Rev. 1.2

IEEE 802.3, IEEE 802.3u, IEEE 802.3ab

USB 3.0 - Backward compatible with USB 2.0/1.1

Chipset ID DisplayLink - DL-3900

VIA/VLI - VL813

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	Dual displays - HDMI + DVI - 2048 x 1152 @ 60Hz Dual displays - HDMI 2048 x 1152 + VGA 1920 x 1200 @ 60Hz

Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	1 - DVI-I (29 pin) 1 - HDMI (19 pin) 2 - USB 3.2 Type-A (9 pin, Fast-Charge) 4 - USB Type-A (9 pin, 5 Gbps) 1 - RJ-45 1 - 3.5 mm Mini-Jack (3 Position) 1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)
-------------------	--

Software

OS Compatibility	Windows 7, 8, 8.1, 10, 11 macOS 10.10 - 10.12, 10.14 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0 , 26.1 Ubuntu 18.04, 20.04, 22.04, 24.04
------------------	---

Special Notes / Requirements

System and Cable Requirements	A host laptop with an available USB-A port.
Note	USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.
	A DVI to VGA adapter is included.

Indicators

LED Indicators	1 - Power
----------------	-----------

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	2A
Output Voltage	20V DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	40W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10-90% non-condensing

Physical Characteristics

Color	Black & Silver
Material	Plastic
Cable Length	39.4 in [1000 mm]
Product Length	8.5 in [21.6 cm]
Product Width	3.4 in [8.6 cm]
Product Height	1.2 in [3.1 cm]

Weight of Product 10.3 oz [291.0 g]

Packaging Information

Package Quantity	1
Package Length	5.6 in [14.2 cm]
Package Width	12.1 in [30.7 cm]
Package Height	2.4 in [6.2 cm]
Shipping (Package) Weight	1.7 lb [0.8 kg]

What's in the Box

Included in Package	1 - docking station
	1 - USB 3.0 cable
	1 - DVI to VGA adapter
	1 - universal power adapter (NA/JP, UK, EU, ANZ)
	1 - quick-start guide

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*