

USB-C Multiport Adapter - USB-C Travel Docking Station w/ 4K HDMI - 60W Power Delivery Pass-Through, GbE, 2pt USB-A 3.0 Hub - Portable Mini USB Type-C Dock for Laptop - White - TAA

Product ID: DKT30CHPDW



This sleek USB-C Multiport Adapter with HDMI combines the capability of three single-function adapters into a portable docking station for your laptop. You get the convenience of a USB-C to USB adapter, USB-C to Ethernet adapter, and USB-C 4K HDMI adapter all in one portable solution.

And, with support for 60W USB Power Delivery 2.0, you can power both the adapter and charge your laptop at the same time.

The versatile USB-C adapter lets you create a dual-monitor workstation virtually anywhere, providing 4K Ultra HD (3840 x 2160p) HDMI output with 30 Hz refresh rate and audio, two USB 3.0 ports, and a Gigabit Ethernet port, with support for USB Power Delivery 2.0.

The Gigabit Ethernet port with support for Wake-on-LAN (WOL), jumbo frames, VLAN tagging, and Energy-Efficient Ethernet, delivers a reliable wired network connection, ideal for areas with limited Wi-Fi access. Plus, with two additional USB 3.0 ports (USB Type-A) you can connect productivity devices like your mouse and/or flash drive.

Ideal for mobile use, the compact multiport adapter supports USB Power Delivery 2.0 (PD 2.0), so you can use your laptop's USB-C power adapter to power both your laptop and the adapter. The adapter also features an integrated extended-length USB-C cable, for added flexibility in connecting to your laptop, which means one less cable to carry with you.

Certifications, Reports and Compatibility





Applications

- The portable adapter, in silver and white, is the perfect accessory for your MacBook Pro, MacBook, Chromebook or other USB-C laptop, adding 4K video, GbE and two USB 3.0 ports
- Power the adapter and your laptop through USB-C, using your laptop's power adapter
- Integrate the compact adapter into small workspaces in offices and home offices
- Connect your laptop to a projector and enjoy multimedia content at home, or display engaging presentations in boardrooms and classrooms
- Use an HDMI port-equipped television in a hotel room as an external display when traveling

Features

- **4-IN-1 TRAVEL DOCK:** USB-C multiport adapter has 4K 30Hz UHD HDMI video output for a single display, 2x USB-A 3.0 (5Gbps) ports, Gigabit Ethernet (GbE), and 60W Power Delivery 2.0 charging pass through
- **EXTRA LONG CABLE:** The portable silver & white USB-C mini dock's 25cm (10 in.) attached cable provides extended reach to reduce port/connector strain on 2-in-1 devices or laptops on riser stands
- **WIDE DEVICE COMPATIBILITY:** USB C multiport adapter for USB-C & Thunderbolt 3 laptops, Ultrabooks, Chromebooks, tablets & phones for brands like HP, Dell, Lenovo, MacBooks, Surface and Samsung Galaxy
- **WIDE OPERATING SYSTEM COMPATIBILITY:** With automatic driver setup, this all-in-one USB 3.1 Gen 1 Type-C docking station supports Windows, macOS, Chrome OS, Ubuntu, Android (Galaxy S9 & up, Pixel 3)
- **POWERED BY LAPTOP OR EXTERNAL ADAPTER:** This dock can draw power from the laptop USB bus or charge the laptop via PD-Passthrough if a USB-C power adapter is connected (12W for dock & 48W for charging)

Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1

Bus Type	USB-C
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	VIA/VLI - VL813 VIA/VLI - VL100 Parade - PS176 ASIX - AX88179

Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	4096 x 2160p @ 24Hz or 3840 x 2160p (HDMI) @ 30Hz
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps) 1 - HDMI (19 pin) 1 - RJ-45 2 - USB Type-A (9 pin, 5 Gbps) 1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)
-------------------	--

Software

OS Compatibility	Windows 7, 8, 8.1, 10, 11<br / >macOS 10.9 to 10.15, 11.3 to 26.1<br / >Chrome OS<br / >Ubuntu 20.04 Kernel 5.15 and up - LTS Versions only
------------------	---

Special Notes / Requirements

System and Cable Requirements	<p>A host laptop with an available USB-C port (to ensure full adapter functionality, the host USB-C port must support USB Power Delivery 2.0 and DP alt mode)</p> <p>Optional: USB-C power adapter (for example, your laptop's USB-C based power adapter)</p>
Note	<p>Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your host USB-C port supports USB Power Delivery 2.0 and DP alt mode.</p> <p>The adapter can connect to a host laptop's USB-C port that doesn't support USB Power Delivery 2.0. However, in this configuration if a power adapter is connected to the multifunction adapter, it will not pass power through to your host laptop.</p> <p>A 4K-capable display is required to achieve 3840 x 2160p resolution (4K is also known as 4K x 2K)</p> <p>USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.</p> <p>Your laptop might have specific charging requirements. For example, if your laptop requires exactly 60W of power and an adapter consumes some of the 60W, your laptop might not recognize that it is getting enough power. For more information about Power Delivery, refer to the manufacturer of your hardware.</p>

Power

Power Source	USB-Powered
Power Delivery	60W

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-10C to 65C (14F to 149F)
Humidity	0~85% RH (Non-condensing)

Physical Characteristics

Color	Silver & White
Material	Plastic
Cable Length	9.8 in [250 mm]
Product Length	13.4 in [34.0 cm]

Product Width	2.0 in [5.1 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	2.3 oz [64.0 g]

Packaging Information

Package Quantity	1
Package Length	8.1 in [20.5 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.7 in [4.2 cm]
Shipping (Package) Weight	6.6 oz [187.0 g]

What's in the Box

Included in Package	1 - USB-C multiport adapter
	1 - quick-start guide

Warranty Information

Warranty	3 Years
----------	---------

****Product appearance and specifications are subject to change without notice.***