

3ft (91cm) Panel Mount DisplayPort Cable - 4K x 2K - DisplayPort 1.2 Extension Cable Male to Female - DP Video Extender Cord with Panel Mount DP Connector - DP Monitor Cable

Product ID: DPPNLFM3



This 3ft panel mount DisplayPort cable features a DisplayPort male connector on one end, and a DisplayPort panel mount (female) molded connector on the other, providing a well-secured, easy to access DisplayPort connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty

Certifications, Reports and Compatibility



Applications

- Extend your DisplayPort interface and allow you screw mount it to a panel

Features

- PANEL MOUNT DISPLAYPORT CABLE:** 3ft (91 cm) DisplayPort v1.2 male to female extender cable; 4K x 2K (3840x2400p 60Hz), 21.6 Gbps bandwidth , HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- RELIABLE DESIGN:** Durable molded female connector with two 4-40 screws to secure on to a machine faceplate/port; Flexible PVC strain relief & jacket prevent fraying/damage due to bending/rough usage; Latching connector prevents accidental disconnection

- **QUALITY CONSTRUCTION:** 28AWG wire with gold-plated pins for improved signal integrity and reliability; DisplayPort panel mount cable / video cord has superior EMI shielding with double sided copper foil to provide higher quality video and audio
- **APPLICATIONS:** Add extra 3ft to your DP cables; DisplayPort extension cable for home/offices/boardrooms/classrooms; works with your professional workstations with FirePro S9000/7000, W8100/7100 graphic cards; Use w/ 1080p/UHD/4K monitors/projector/display
- **SPECS:** 3 foot (91 cm) Black DisplayPort 1.2 DP Latching Male to DP Female (panel mountable w/ 2x 4-40 UNC screws) 28 AWG PVC cable jacket, ABS connector shell Shield: Double sided copper foil Backward compatible w/ DP1.1 Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG

Connector(s)

Connector A	1 - DisplayPort (20 pin)
Connector B	1 - DisplayPort (20 pin)

Environmental

Operating Temperature	-20C to 80C
Storage Temperature	-20C to 80C
Humidity	15 to 65%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	3.0 ft [0.9 m]
Cable OD	0.3 in [7.3 mm]
Product Length	36.8 in [93.5 cm]

Product Width	1.3 in [3.4 cm]
Product Height	0.8 in [2.0 cm]
Weight of Product	2.5 oz [71.0 g]

Packaging Information

Package Quantity	1
Package Length	7.2 in [18.2 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.9 in [2.2 cm]
Shipping (Package) Weight	3.2 oz [92.0 g]

What's in the Box

Included in Package	1 - 3ft DisplayPort Extension Panel Mount Cable
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

