

6 ft DVI-D Single Link Cable - M/M

Product ID: DVIMM6



The DVIMM6 DVI-D Single Link cable features 2 male DVI (19-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 6ft DVI-D male to male cable supports resolutions of up to 1920x1200 and transmission rates of up to 4.95 Gbits/sec, and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect your desktop or laptop computer to a DVI-D Single Link display or projector

Features

- Supports resolutions up to 1920x1200
- High-speed digital transmission rate of up to 4.95 Gbits/sec
- Aluminum-Mylar Foil with Braided Shielding

- Supports hot-plugging of DVI display devices
- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Performance

Maximum Data Transfer Rate	4.95 Gbits/sec
----------------------------	----------------

Connector(s)

Connector A	1 - DVI-D (19 pin)
Connector B	1 - DVI-D (19 pin)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	5.4 oz [154.0 g]

Packaging Information

Package Quantity	1
Package Length	7.5 in [19.1 cm]
Package Width	7.8 in [19.7 cm]

Package Height 1.3 in [3.4 cm]

Shipping (Package) Weight 6.8 oz [194.0 g]

What's in the Box

Included in Package 1 - 6 ft DVI-D Single Link LCD Flat Panel Monitor Cable - M/M

**Warranty
Information**

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

