

3 ft Shielded External eSATA Cable M/M

**Product ID:** ESATA3



This shielded eSATA cable offers a high quality 3ft connection between a desktop or laptop computer and external SATA storage devices, allowing you to "externalize" the impressive capabilities offered by Serial ATA.

## Certifications, Reports and Compatibility



## Applications

## Features

- Compliant with Serial ATA III Specifications  
Fast data transfer rate of up to 6 Gbps

---

### Connector(s)

Warranty	Lifetime
Connector A	1 - eSATA (7 pin, Data)
Connector B	1 - eSATA (7 pin, Data)

---

### Environmental

Operating Temperature	20C ~ 80C (68F ~ 176F)
-----------------------	------------------------

Storage Temperature 23C ~ 25C (73F ~ 77F)

Humidity 40% ~ 60%

---

**Physical Characteristics**

Color	Black
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.4 in [0.9 cm]
Weight of Product	2.3 oz [66.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.9 in [14.9 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.6 in [1.6 cm]
Shipping (Package) Weight	2.2 oz [62.0 g]

---

**What's in the Box**

Included in Package	1 - 3 ft Shielded External eSATA Cable M/M
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*