

Citrix EW3A0000712 Compatible SFP Module - 1000BASE-LX - 1GbE Single Mode Fiber SMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 10km - 1310nm - DDM

**Product ID:** EW3A0000712-ST



The EW3A0000712-ST is a Citrix EW3A0000712 compatible fiber transceiver module that has been designed, programmed and tested to work with Citrix brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-LX compliant networks, with a maximum distance of up to 10 km (6.2 mi).

**Technical Specifications:**

- Wavelength: 1310nm
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 634,210,013 hours
- Power Consumption: < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

### Features

- 100% CITRIX EW3A0000712 COMPATIBLE SFP TRANSCEIVER: Designed, programmed and tested to work with compatible Citrix switches and routers to deliver reliable 1GbE connectivity
- TECHNICAL SPECS: 1000BASE-LX 1Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Citrix routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Citrix
Industry Standards	IEEE 802.3z 1000BASE-LX

---

### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nm
Fiber Operating Mode	Full-Duplex
DDM	Yes

---

Compatible Networks	1000 Mbps (1 Gbps)
MTBF	634,210,013 hours
Power Consumption (In Watts)	< 1.3W

---

#### **Physical Characteristics**

Product Length	0.5 in [1.4 cm]
Product Width	2.2 in [5.7 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	0.6 oz [18 g]

---

#### **Packaging Information**

Package Length	4.4 in [11.2 cm]
Package Width	3.7 in [9.4 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	1.7 oz [48.0 g]

---

#### **What's in the Box**

Included in Package	1 - SFP Transceiver
---------------------	---------------------

---

#### **Warranty Information**

Warranty	Lifetime
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***

