

TV Ceiling Mount - Full-Motion Universal Hanging Single Screen Mount with Adjustable Telescopic Long Pole - Tilt / Swivel - VESA Bracket for 32"-75" Displays

Product ID: FPCEILPTBLP



StarTech.com

This ceiling TV mount supports VESA mount compatible TVs from 32" to 75" in size, with a weight capacity of up to 110 lb. (50 kg). It lets you save wall and floor space by hanging your flat-panel LCD, LED or plasma TV from the ceiling in a prominent area.

The ceiling mount is ideal for use in lobbies, entrances or other areas with high ceilings.

With a telescopic pole, the TV mount lets you suspend a display at your desired distance from the ceiling. This works well with a range of ceiling heights. The steel pole can extend from 8.2 to 9.84 ft. (2.5 to 3 m), with a total lift (height extension) of 19.6" (.5 m).

The flat-screen ceiling mount accommodates a wide variety of ceiling types. You can swivel the TV to work with virtually any type of ceiling for level viewing, including sloped ceilings (up to 60 degrees), and pitched or horizontal (flat) ceilings.

You can adjust your TV to create a comfortable viewing angle, by tilting it up to -25 degrees down towards your audience for optimum visibility. Plus, the full-motion mount lets you swivel your display around the pole + 180 / - 180 degrees, without using tools.

Simply attach the included vertical brackets, with built-in hooks, to the back of your TV. Once attached, hang your TV securely onto the ceiling mount. The +/-3 degree post-installation leveling adjustments ensure ideal positioning after hanging.

FPCEILPTBLP is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Suspend a flat-screen TV in an area with a high ceiling
- Ideal for lobbies and entrance ways
- Keep your guests informed and entertained

Features

- **SINGLE 75" TV CEILING MOUNT:** VESA compatible ceiling mount supports displays up to 75" (110lb/50kg) including curved TVs; Height adjustable pole, 98.4" - 118.1" (250cm - 300cm) from ceiling
- **FULL MOTION:** Ceiling TV mount allows for the display to be swiveled 180 around the telescopic pole, and tilt downwards -25 degrees, without using tools
- **VERSATILE INSTALLATION:** Adjustable mounted ceiling bracket for TV / screen allows the pole to be adjusted and secured +/-60 degrees for angled/sloped/slanted ceilings to ensure displays are level
- **COMPATIBILITY:** Universal hanging TV ceiling mount supports LG, Samsung, Sony, and Sharp TVs among others (screws/spacers incl) & VESA hole patterns of 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 600x200, 600x300, 600x400
- **TIDY AESTHETIC:** The universal television ceiling mount for one large display provides a hook-and-mount design for easy setup and integrated cable management; ideal for digital signage applications

Hardware

Warranty	5 Years
Wallmountable	No
Cable Management	Yes
# of Displays Supported	1
Mounting Options	Ceiling Mount
VESA Hole Pattern(s)	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm

300x300 mm

400x200 mm

400x300 mm

400x400 mm

600X200 mm

600x300 mm

600x400 mm

Performance

General Specifications	Post-Installation Leveling Adjustment: +/-3
Weight Capacity (Per Display)	110.2 lb [50 kg]
Minimum Display Size	32"
Maximum Display Size	75"
Fits Curved Display	Yes
Video Wall	No
Height Adjustment	Yes
Minimum Height	8.2 ft [2.5 m]
Maximum Height	9.8 ft [3 m]
Display Tilt	+0 / -25
Swivel / Pivot	+180 to -180
Anti-theft	No

Physical Characteristics

Color	Black
Material	Steel
Product Length	26.8 in [68.0 cm]
Product Width	17.1 in [43.5 cm]

Product Height	10.6 ft [3.2 m]
Weight of Product	22.0 lb [10.0 kg]

Packaging Information

Package Quantity	1
Package Length	4.2 ft [1.3 m]
Package Width	12.7 in [32.3 cm]
Package Height	4.8 in [12.3 cm]
Shipping (Package) Weight	23.2 lb [10.5 kg]

What's in the Box

Included in Package	1 - ceiling mount and pole
	1 - middle pole
	1 - lower pole
	1 - TV mount
	2 - vertical brackets
	1 - horizontal bracket
	2 - M8x55 mm screws
	2 - M8x60 mm screws
	4 - nuts
	1 - wrench
	1 - hex key
	1 - mounting template
	4 - M5x14 mm screws
	4 - M6x14 mm screws
	4 - M6x30 mm screws
	4 - M8x30 mm screws

- 4 - M8x50 mm screws
- 4 - rectangular washers
- 8 - small spacers
- 8 - large spacers
- 4 - screws
- 4 - concrete anchors
- 4 - circular washers
- 1 - instruction manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

