

Full Motion TV Wall Mount - Heavy Duty Articulating TV Wall Mount Bracket for 32" to 75" (165lb/75kg) VESA Display - Universal Adjustable Tilt/Swivel Flat Screen Arm - Silver - TAA

Product ID: FPWARPS



Strong and sleek, this full-motion TV wall mount lets you free up space by wall-mounting your 32" to 75" TV, and adjust it to the right viewing position with ease.

Once it's installed, the flat-screen TV wall mount is simple to adjust without using tools. You can extend the arms with ease to position your TV anywhere from 4.1" to 21.6" (105 to 550 mm) away from the wall. The TV mount swivels +/-60 degrees and tilts +/-15 degrees for optimum viewing.

This premium television wall mount beautifully combines form and function. Designed to provide an impressive appearance in every position, the premium black and silver design makes it ideal in a company lobby or hallway, information kiosk, or living space. With the arms extended, the protective covers provide a tidy, professional look. The cable-management channel inside the arms keeps cables neatly tucked away.

Engineered with steel and aluminum, the robust TV mount securely supports a TV with a maximum weight capacity of 165 lb. (75 kg).

FPWARPS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Wall-mount your TV in a boardroom, lobby, lecture hall, classroom or meeting space

- Keep guests informed or entertained in hotels, restaurants and other hospitality venues
- Save space by wall-mounting your TV in your home theater or living room

Features

- **LARGE 75" TV WALL MOUNT:** Heavy-duty full horizontal motion TV wall mount supports VESA compatible displays from 32 to 75 inch (165 lb/75 kg) w/ a durable full-motion steel frame & premium silver powder-coated finish
- **WIDE RANGE OF MOTION:** Full motion TV wall mount offers +/-60 swivel, +/-15 tilting to find the ideal viewing angle; Articulating extendable arms reach out to 21.6" (550mm) from the wall & fold in to 4.1" (105mm) for a lower profile
- **COMPATIBILITY:** Universal LCD/LED television mount supports LG, Samsung, Sony, Sharp, others (screws/spacers incl) & VESA bracket hole patterns 200x300, 200x400, 300x200, 300x300, 400x200, 400x300, 400x400, 500x300, 600x300, 600x400, 800x400, 800x500
- **PREMIUM FINISH:** Silver steel & aluminum mount designed to have a professional look; Decorative covers maintain the high quality aesthetic no matter how the LCD/LED flat screen is positioned
- **FLEXIBLE INSTALLATION:** Adjustable TV wall mounting bracket is installed on a single stud for flexible positioning (ie. corner mounting); Integrated cable management; ideal for customer-facing digital signage, retail & education

Hardware

Warranty	5 Years
Wallmountable	Yes
Cable Management	Yes
# of Displays Supported	1
Mounting Options	Wall-Mount
VESA Hole Pattern(s)	200x100 mm
	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm

400x400 mm

500x300 mm

600x300 mm

600x400 mm

800x400 mm

800x500 mm

810x500 mm

Performance

General Specifications	Minimum Distance to Wall: 4.13" (105 mm) Maximum Distance to Wall: 21.65" (550 mm)
Weight Capacity (Per Display)	165.4 lb [75 kg]
Minimum Display Size	32"
Maximum Display Size	75"
Fits Curved Display	Yes
Video Wall	No
Display Tilt	+ 15 / - 15
Swivel / Pivot	+ 60 / - 60

Physical Characteristics

Color	Black & Silver
Material	Steel
Product Length	34.1 in [86.5 cm]
Product Width	20.5 in [52.0 cm]
Product Height	20.6 in [52.4 cm]
Weight of Product	22.8 lb [10.3 kg]

**Packaging
Information**

Package Quantity	1
Package Length	18.5 in [47.1 cm]
Package Width	36.1 in [91.8 cm]
Package Height	6.1 in [15.5 cm]
Shipping (Package) Weight	27.8 lb [12.6 kg]

What's in the Box

Included in Package	1 - TV Wall-Mount Assembly
	2 - Vertical Brackets
	1 - 6 mm Hex Key
	2 - Vertical Bracket Screws
	8 - Concrete Anchors
	8 - Wall Screws
	4 - M4 x 12 mm Screws
	4 - M4 x 18 mm Screws
	4 - M5 x 12 mm Screws
	4 - M6 x 12 mm Screws
	4 - M6 x 18 mm Screws
	4 - M8 x 12 mm Screws
	4 - Flat Washers
	4 - M8 x 18 mm Screws
	1 - User Manual

**Warranty
Information**

Warranty	5 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*