

Cisco GLC-EX-SMD Compatible SFP Module - 1000BASE-EX - 1GbE Single Mode Fiber SMF Optic Transceiver - 1GE Gigabit Ethernet SFP - LC 40km - 1310nm - DDM Cisco Firepower, ASR920, IE2000

**Product ID:** GLCEXSMDST



The GLCEXSMDST is a Cisco GLC-EX-SMD compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-EX compliant networks, with a maximum distance of up to 40 km (24.8 mi).

**Technical Specifications:**

- Wavelength: 1310 nm
- Maximum Data Transfer Rate: 1.25 Gbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 40 km (24.8 mi)
- MTBF: 3,013,496 hours
- Power Consumption: Less than 1 Watt
- Digital Diagnostics Monitoring (DDM): Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

## Features

- 100% CISCO GLC-EX-SMD COMPATIBLE: Works with Cisco switches like Firepower, ASR920, IE2000, IE4000, ASR1000 and others
- TECHNICAL SPECS: 1000BASE-EX 1 Gbps Single Mode (SMF) LC Connector 1310nm Digital Diagnostic Monitoring (DDM) Distances up to 40km (24.8mi)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3z 1000BASE-EX

---

### Performance

Maximum Data Transfer Rate	1.25 Gbps
Max Transfer Distance	40 km (24.8 mi)
Type	Single Mode
Wavelength	1310nm

Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	3,013,496 hours
Power Consumption (In Watts)	< 1 W

---

**Connector(s)**

Local Unit Connectors	1 - Fiber Optic LC Duplex
-----------------------	---------------------------

---

**Special Notes / Requirements**

Note	For use in Gigabit fiber networking equipment and media converters
------	--------------------------------------------------------------------

---

**Environmental**

Operating Temperature	0°C to 70°C (32°F to 158°F)
Storage Temperature	-40°C to 85°C (-40°F to 203°F)
Humidity	5% - 95% RH

---

**Physical Characteristics**

Color	Silver
Product Length	2.2 in [56.6 mm]
Product Width	0.5 in [1.4 cm]
Product Height	0.5 in [1.2 cm]
Weight of Product	0.7 oz [19.0 g]

---

**Packaging Information**

Package Length	4.3 in [11.0 cm]
Package Width	3.7 in [9.4 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	1.8 oz [50.0 g]

**What's in the Box**

Included in Package	1 - SFP transceiver
---------------------	---------------------

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

