

Cisco GLC-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m - Cisco Firepower, ASR920, IE2000

Product ID: GLCTST



The GLCTST is a Cisco GLC-T compatible copper transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 1000 Mbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 4,655,371 hours
- Power Consumption: Less than 1.3 Watts
- Digital Diagnostics Monitoring (DDM): No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Replacing defective or damaged SFP modules in Cisco switches and routers
- Expand your network to remote segments

Features

- 100% CISCO GLC-T COMPATIBLE: Works with Cisco switches like Firepower, ASR920, IE2000, IE4000, ASR9000 and others
- TECHNICAL SPECS: 1000BASE-T 1 Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3ab 1000BASE-T

Performance

Maximum Data Transfer Rate	1000 Mbps
Max Transfer Distance	100m [328ft]
Type	Copper
DDM	No
Compatible Networks	1000 Mbps (1 Gbps)
MTBF	4,655,371 hours
Power Consumption (In)	< 1.3 W

Watts)

Connector(s)

Local Unit Connectors	1 - RJ-45
-----------------------	-----------

Special Notes / Requirements

Note	For use in 1 Gigabit networking equipment and media converters
------	--

Power

Output Voltage	3.3V DC
----------------	---------

Environmental

Operating Temperature	0C to 70C (32F to 158F)
-----------------------	-------------------------

Storage Temperature	-40C to 85C (-40F to 185F)
---------------------	----------------------------

Humidity	30~75% RH
----------	-----------

Physical Characteristics

Color	Silver
-------	--------

Product Length	2.7 in [68.0 mm]
----------------	------------------

Product Width	0.5 in [1.2 cm]
---------------	-----------------

Product Height	0.6 in [1.4 cm]
----------------	-----------------

Weight of Product	0.9 oz [25.0 g]
-------------------	-----------------

Packaging Information

Package Length	4.4 in [11.3 cm]
----------------	------------------

Package Width	3.6 in [9.1 cm]
---------------	-----------------

Package Height	1.3 in [3.4 cm]
----------------	-----------------

Shipping (Package) Weight	1.8 oz [52.0 g]
---------------------------	-----------------

What's in the Box

Included in Package	1 - SFP transceiver
---------------------	---------------------

Warranty Information

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*

