

10ft (3m) Micro HDMI to HDMI Cable w/ Ethernet, 4K 30Hz Video, Durable High Speed Micro HDMI Type-D to HDMI 1.4 Adapter Cable/Converter Cord, UHD HDMI Monitors/TVs/Displays - M/M

Product ID: HDADMM3M



The HDADMM3M 3m (10ft) HDMI Micro to HDMI Cable with Ethernet is designed to connect devices that feature an HDMI Micro port to an HDMI-enabled display/device, providing a cost-saving solution for connecting cutting-edge and next-generation HDMI-enabled devices to existing HDMI technology.

High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Constructed with 34 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

<small>The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.**</small>**

Certifications, Reports and Compatibility



Applications

- Connect your smartphone or other HDMI Micro-equipped portable device to your HDMI-enabled TV or display

Features

- HIGH SPEED MICRO HDMI to HDMI CABLE: 3m HDMI 1.4b adapter cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- DURABLE: Ultra HD high speed fully molded Micro HDMI to HDMI converter cable w/ durable PVC jacket for high strength/reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending/rough usage; Ideal for commercial environment
- QUALITY CONSTRUCTION: Micro HDMI to HDMI video cord constructed with 32AWG wire & gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- APPLICATIONS: This adapter connects Micro HDMI (Type-D) devices such as phones, tablets, laptops and cameras (DSLR/Video) to your HDMI (Type-A) TV, monitor, display, projector; Ideal for viewing on larger screens; Samsung/Sony/Apple TV/Dell/LG
- SPECS: 3 m Black HDMI 1.4b HDMI Male (Type-D/Micro) to HDMI Male (Type-A/Standard) 32 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
MTBF	HDMI end is 10000+ times and Micro HDMI end is 5000+ times insertion rating.

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - Micro HDMI (19 pin)

Physical Characteristics

Color	Black
-------	-------

Wire Gauge	32 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	3.1 oz [88.0 g]

Packaging Information

Package Quantity	1
Package Length	6.5 in [16.4 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	3.2 oz [90.0 g]

What's in the Box

Included in Package	1 - 3m High Speed HDMI Cable with Ethernet - HDMI to HDMI Micro - M/M
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***

