

3ft (91cm) Slim HDMI Cable, 4K High Speed HDMI Cable with Ethernet, 4K 30Hz UHD HDMI Cord, 10.2 Gbps Bandwidth, HDMI 1.4 Video / Display Cable 36AWG, HDCP 1.4 - Thin HDMI Cable

Product ID: HDMIIMM3HSS



This Slim High Speed HDMI Cable with Ethernet is compatible with HDMI-capable devices, and features a thin cable design (3.5mm in diameter).

High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz), 1080p+ at up to 120Hz refresh rate, and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Constructed with 36 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Allows multiple High Speed HDMI-equipped devices to share Internet connection (satellite receivers, DVD players,

A/V receivers, High Definition TVs, game consoles and more)

- Connect HDMI-equipped devices like LCD TVs, LCD Projectors, Plasma TVs, HDTVs and DVD Players

Features

- HIGH SPEED HDMI CABLE: 3ft (91cm) Slim HDMI Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- SLIM AND DURABLE: Ultra HD slim (0.14"/3.6mm OD) HDMI cable w/ durable PVC jacket & strain relief for high strength/reliability; Thin HDMI cable w/ a low profile design that reduces bend radius & improves flexibility; Ideal for Commercial environments
- QUALITY CONSTRUCTION: 36AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid (85% coverage) improve signal integrity and reliability, providing higher quality video and audio
- APPLICATIONS: Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- SPECS: 3 ft (91 cm) Black HDMI 1.4b HDMI Cord Male to Male 36 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil w/ 85% Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Humidity	0%- 95% (non-condensing) at 25°C

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	36 AWG
Cable Length	3.0 ft [0.9 m]
Cable OD	0.1 in [3.6 mm]
Product Length	36.0 in [91.5 cm]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	1.1 oz [32.0 g]

Packaging Information

Package Quantity	1
Package Length	5.9 in [14.9 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.7 in [1.8 cm]
Shipping (Package) Weight	1.6 oz [44.0 g]

What's in the Box

Included in Package	1 - 3 ft Slim High Speed HDMI Cable with Ethernet - HDMI -M/M
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*