

3ft (91cm) HDMI Female to Male Adapter, 4K High Speed Panel Mount HDMI Cable, 4K 30Hz UHD HDMI, 10.2 Gbps Bandwidth, 4K HDMI Female to HDMI Male, HDMI Panel Mount Connector Cable

Product ID: HDMIIPNLFM3



The HDMIIPNLFM3 3ft High Speed HDMI Cable for Panel Mount features an HDMI male connector on one end, and an HDMI panel mount (female) molded connector on the other, providing a well-secured, easy to access HDMI connection on any machine port or faceplate.

Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend your HDMI interface and screw mount it to a panel

Features

- HIGH SPEED PANEL MOUNT CABLE:** 3 ft (91 cm) HDMI 1.4b cable supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- DURABLE:** HDMI Ultra HD cable with durable PVC jacket for high strength and reliability; Molded female connector with two 4-40 (0.31"/8mm long) screws to secure on to a machine faceplate/port; Ideal for Commercial environments

- **QUALITY CONSTRUCTION:** 28AWG wire, corrosion resistant gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Allows easy access to HDMI ports on your computer/laptop/desktop/workstation; Connect TV/monitor/display/projector; Ideal for use in retail kiosk/booth/lecture podium/embedded applications; Samsung/Sony/Apple TV/Dell/LG
- **SPECS:** 3 ft (91 cm) Black HDMI 1.4 HDMI Male to Female (panel mountable with two 4-40 screws) 28 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC, YCC601 Color Supports HDMI 1.4 and earlier

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	5C - 70C
Storage Temperature	-10C - 80C
Humidity	0-85%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	3.0 ft [0.9 m]
Cable OD	0.3 in [6.5 mm]
Product Length	36.0 in [91.4 cm]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.0 cm]
Weight of Product	2.9 oz [81.0 g]

**Packaging
Information**

Package Quantity	1
Package Length	7.2 in [18.3 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.7 in [1.9 cm]
Shipping (Package) Weight	3.1 oz [88.0 g]

What's in the Box

Included in Package	1 - 3 ft Standard HDMI Cable for Panel Mount - F/M
---------------------	--

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

