

40ft (12m) High Speed HDMI Cable M/M - 4K @ 30Hz - No Signal Booster Required

Product ID: HDMM40



This High Speed HDMI Cable is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

#### High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and multi-channel audio, you can enjoy a fully immersive viewing and listening experience.

Constructed with 24 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

#### Certifications, Reports and Compatibility



#### Applications

- Connect high-definition A/V devices such as streaming media players, Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

## Features

- Supports Ultra HD Resolutions up to 3840x2160 (4K x 2K)
- Provides connection distances up to 40 feet away
- Guaranteed reliability with our lifetime warranty

---

### Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

---

### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	60% at 25C

---

### Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	40.0 ft [12.2 m]
Cable OD	0.4 in [10 mm]

---

Product Length	40.0 ft [12.2 m]
Product Width	0.8 in [2.0 cm]
Product Height	0.7 in [1.7 cm]
Weight of Product	2.9 lb [1.3 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	10.0 in [25.5 cm]
Package Width	9.7 in [24.7 cm]
Package Height	3.0 in [7.7 cm]
Shipping (Package) Weight	2.8 lb [1.3 kg]

---

**What's in the Box**

Included in Package	1 - 40ft High Speed HDMI Cable - HDMI - M/M
---------------------	---

---

**Warranty Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

