

16.4ft (5m) HDMI Cable - 4K High Speed HDMI Cable with Ethernet - UHD 4K 30Hz Video - HDMI 1.4 Cable - Ultra HD HDMI Monitors, Projectors, TVs & Displays - Black HDMI Cord - M/M

Product ID: HDMM5M



This High Speed HDMI Cable with Ethernet is designed to deliver superior video and audio performance while ensuring reliable connectivity with a variety of HDMI devices, including HDTVs, stereo receivers, projectors, gaming consoles, and more.

High Speed HDMI

This HDMI 1.4b cable supports Ultra HD 4K resolutions (3840x2160p at 30Hz, or 4096x2160p at 24Hz), Full HD (1920x1080p at up to 120Hz), and a bandwidth of 10.2 Gbps for seamless video and audio transmission. It also supports wide aspect ratios, making it perfect for both home entertainment systems and professional presentations. With support for 3D video and 8-channel audio (5.1/7.1/Dolby Digital Plus/Dolby TrueHD), you can enjoy a fully immersive viewing and listening experience.

Premium Build Quality

Constructed with 30 AWG copper wire, gold-plated connectors, and superior EMI shielding using Al-Mylar foil and a copper braid, this cable minimizes signal loss and interference. This ensures clear, high-quality audio and video transmission with exceptional reliability.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

Features

- **HIGH SPEED HDMI CABLE:** 16.4 ft (5m) HDMI 1.4b Cable with Ethernet supports 4K video (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- **DURABLE:** 16.4ft Ultra HD 4K high speed HDMI cable (fully molded) with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying/damage due to repetitive bending or rough usage
- **QUALITY CONSTRUCTION:** 30/28 AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil & copper braid improve signal integrity and reliability, providing higher quality video & audio with this HDMI 1.4 cable
- **APPLICATIONS:** Use this 4K HDMI cable in home offices, conference rooms, offices or classrooms; works with your laptop, professional workstation & soundbar for presentations via UHD/4K monitor, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- **SPECS:** 16.4 foot (5m) Black HDMI 1.4b HDMI Cord Male to Male 30/28 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil w/ 65% Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color Supports HDMI 1.4 and earlier Lifetime Warranty

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 70C (-4F to 158F)

Humidity 0 to 95% (non-condensing) at 25C

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	28/30 AWG
Cable Length	16.4 ft [5 m]
Product Length	16.4 ft [5.0 m]
Product Width	0.8 in [2.1 cm]
Product Height	0.4 in [1.1 cm]
Weight of Product	11.2 oz [316.0 g]

Packaging Information

Package Quantity	1
Package Length	13.8 in [35.0 cm]
Package Width	5.1 in [13.0 cm]
Package Height	1.6 in [4.1 cm]
Shipping (Package) Weight	11.4 oz [322.0 g]

What's in the Box

Included in Package	1 - 5m High Speed HDMI Cable - HDMI - M/M
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***