

16.4ft (5m) Premium Certified HDMI 2.0 Cable with Ethernet - High Speed Ultra HD 4K 60Hz HDMI Cable HDR10 - Long HDMI Cord (Male/Male Connectors) - For UHD Monitors, TVs, Displays

**Product ID:** HDMM5MP



This High Speed HDMI cable has been tested in accordance with the Premium HDMI Cable Certification Program. This ensures it's able to deliver the newest technical features that the latest HDMI specifications have to offer, including enhanced resolutions and protection against EMI interference.

Each of our certified Premium High Speed HDMI Cables is labeled with unique anti-counterfeiting authentication, so you can be confident that you have received a genuine certified cable.

The cable supports resolutions of up to 4K@60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR (High Dynamic Range) for higher contrast ratio and vivid colors.

With higher resolutions, increased speeds, and sharper images, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI capabilities available today. It's the perfect cable for creating dependable home theater connections or providing lifelike digital signage.

Plus, the cable also supports up to 32 uncompressed digital audio channels to provide crystal-clear sound. The cable is also backward compatible with previous HDMI specifications and will work with all of your existing HDMI devices.

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center. This gives you the assurance that the cable will deliver the high-bandwidth enabled features you need. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

The cable delivers dual video streams so that you can view two videos simultaneously on the same display. Your display must support Multi-View in order to take advantage of dual video streams.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

## Certifications, Reports and Compatibility



## Applications

- Connect 4K/Ultra HD displays and devices

## Features

- **HIGH PERFORMANCE:** 16.4 ft (5m) Premium Certified HDMI 2.0 Cable with Ethernet, 4K 60Hz (3840x2160p), 18Gbps bandwidth, HDR10 for high contrast ratio, Ultra wide aspect ratio, 32 Ch. multi-stream audio w/1536Hz sampling (5.1/7.1/DD+/Dolby TrueHD/Atmos)
- **DURABLE:** Ultra HD high speed fully molded 4K 60Hz HDMI cable with durable PVC jacket for high strength and reliability; Flexible PVC strain relief prevents fraying or damage due to repetitive bending or rough usage
- **QUALITY CONSTRUCTION:** 26AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and copper braid improve signal integrity and reliability, providing higher quality video and audio
- **APPLICATIONS:** Ideal for home/office and travel, works with computer/laptop/desktop/workstation; Long UHD HDMI cord to connect your TV/monitor/display/projector; Samsung/Sony/Apple TV/Dell/LG; Compatible with HDMI 1.4 1080p HD and previous HDMI versions
- **SPECS:** 16.4 feet (5 meters) Black HDMI 2.0 Male to Male HDMI cable 26 AWG PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 2.2, CEC, BT.2020 colorimetry Lifetime Warranty

---

### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Gold                           |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

---

### Performance

|                             |   |
|-----------------------------|---|
| Maximum Digital Resolutions | 3840 x 2160 (Ultra HD 4K) @ 60hz                  |
| Audio Specifications        | Up to 32 audio channels with 1536Hz sampling rate |

---

### Connector(s)

|             |                   |
|-------------|-------------------|
| Connector A | 1 - HDMI (19 pin) |
| Connector B | 1 - HDMI (19 pin) |

---

**Environmental**

|                       |                         |
|-----------------------|-------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature   | 0C to 50C (32F to 122F) |
| Humidity              | 0% ~ 85%RH              |

---

**Physical Characteristics**

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Connector Style   | Straight          |
| Wire Gauge        | 26 AWG (0.404 mm) |
| Cable Length      | 16.4 ft [5 m]     |
| Product Length    | 16.4 ft [5 m]     |
| Weight of Product | 0.0 oz [0.5 g]    |

---

**Packaging Information**

|                           |                   |
|---------------------------|-------------------|
| Package Quantity          | 1                 |
| Package Length            | 8.5 in [21.6 cm]  |
| Package Width             | 9.5 in [24.2 cm]  |
| Package Height            | 1.6 in [4.1 cm]   |
| Shipping (Package) Weight | 15.5 oz [438.0 g] |

---

**What's in the Box**

|                     |                |
|---------------------|----------------|
| Included in Package | 1 - HDMI cable |
|---------------------|----------------|

---

**Warranty Information**

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

***\*Product appearance and specifications are subject to change without notice.***