

3ft (1m) Premium Certified HDMI 2.0 Cable, High Speed Ultra HD 4K 60Hz HDMI Cable w/ Ethernet, HDR10, ARC, TPE Jacket, UHD HDMI Video Cord, For UHD Monitors, TVs, Displays - M/M

Product ID: HDMMV1M



This Premium High Speed HDMI 2.0 Certified Cable withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, this durable cable is a must-have for both business and consumer applications.

Experience the latest that HDMI 2.0 has to offer

This high performance 4K cable supports resolutions of up to 4K at 60Hz (3840x2160p) and bandwidths of up to 18Gbps. It also supports HDR10 (High Dynamic Range) and Dolby Vision for higher contrast ratio and vivid colors.

Plus, ARC (Audio Return Channel) has up to 32 uncompressed 5.1 and 7.1 digital audio channels to support DTS-HD Master Audio, DTS:X, Dolby TrueHD, Dolby Atmos for high quality sound.

With high resolutions, increased speeds, sharper images, and crystal-clear audio, you can expect an enhanced video experience. The cable is guaranteed to provide the very best HDMI 4K performance available today. It's the perfect cable for creating the ultimate home theater or for providing lifelike digital signage.

This cable works with all 4K ready devices and is also backward compatible with previous HDMI specifications.

Provide superior connections with Premium High Speed certification

The cable has undergone rigorous compliance testing and is certified by an HDMI Authorized Test Center to ensure it supports the high bandwidth enabled features it promises. An EMI test is also performed to ensure the cable minimizes interference with wireless signals.

Cable Key Features

Aluminum-mylar foil with braided shielding improve EMI protection

Long lasting flexible TPE jacket & strain relief (TPE is non-toxic & halogen free for environmental sustainability)

Connector Key Features

Corrosion-free gold-plated connectors ensure premium video quality & enhanced reliability

Tested to withstand 10,000+ insertions

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

Features

- **HIGH PERFORMANCE CABLE:** 3.3ft (1m) Premium Certified High Speed HDMI cable with Ethernet supports 4K 60Hz (3840x2160), 18Gbps bandwidth, HDR10, Ultra wide aspect ratio, 32 Ch Audio (5.1/7.1/Dolby TrueHD/Atmos), ARC, BT.2020 colorimetry, 3D video
- **PREMIUM HDMI 2.0 CABLE:** Ultra HD 4K 60Hz HDMI cord is engineered & built to improve signal integrity; Featuring corrosion free gold-plated connectors encased in die-cast aluminium to prevent signal degradation due to EMI
- **DURABLE:** Tested to withstand 10,000+ insertions & 600+ bend cycles at 120 angle; TPE outer jacket with molded strain relief absorbs stress from frequent bends; TPE is flexible, environmentally friendly, non-toxic, halogen-free, and RoHS compliant
- **APPLICATIONS:** Ideal for home/office & travel, works with computer/laptop/desktop/PC/workstation; UHD HDMI cord to connect your TV/monitor/display/projector; Samsung/Sony/Apple TV/Dell/LG; Works w/ HDMI 2.0 Ultra HD, 1080p Full HD & previous HDMI versions
- **SPECS:** 3.3 feet (1 meter) - HDMI 2.0 - Premium Certified HDMI Cable - High Speed Cable with Ethernet - HDMI Male to Male - Outer Diameter: 0.24" (6.5 mm) - 30 AWG - TPE Jacket w/Al-Mylar braid - Gold-plated Connectors w/Die-cast Aluminum Shielding

Hardware

Warranty	Lifetime
Active or Passive Adapter	Passive
Number of Conductors	19
Connector Plating	Gold

Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Video Revision	HDMI 2.0b
Maximum Data Transfer Rate	18Gbps
Maximum Cable Length	3.3 ft [1 m]
Maximum Digital Resolutions	4K 60Hz 3840x2160
Audio Specifications	HDMI - 32 Channel Audio
	HDMI - 7.1 Channel Audio
	HDMI - 5.1 Channel Audio

Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	0C to 50C (32F to 122F)
Humidity	0%RH ~ 85%RH

Physical Characteristics

Color	Black
Wire Gauge	30 AWG
Cable Length	3.3 ft [1 m]
Cable OD	0.2 in [6 mm]
Product Length	39.4 in [100.0 cm]
Product Width	0.8 in [2.0 cm]
Product Height	0.4 in [1.1 cm]

	Weight of Product	3.1 oz [88.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	7.6 in [19.2 cm]
	Package Width	7.7 in [19.6 cm]
	Package Height	0.9 in [2.2 cm]
	Shipping (Package) Weight	2.7 oz [76.0 g]
What's in the Box		
	Included in Package	1 - Premium High Speed HDMI Cable
Warranty Information		
	Warranty	Lifetime

****Product appearance and specifications are subject to change without notice.***