

35ft (10.6m) Plenum Rated HDMI Cable, 4K High Speed Long HDMI Cord w/ Ethernet, 4K30Hz UHD, 10.2 Gbps, HDCP 1.4, In Wall Plenum HDMI 1.4 Display Cable, HDMI Computer to TV Cable

**Product ID:** HDPMM35



The plenum-rated High Speed HDMI® cable can be installed in air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

This cable features 2 gold-plated HDMI (male) connectors and durable construction to provide you with a dependable HDMI to HDMI connection between your A/V devices.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

About StarTech.com HDMI to HDMI Cables:

StarTech.com High Speed HDMI digital video and audio cables are expertly designed and constructed of only top quality materials to ensure high-quality, high-definition performance. The HDMI standard combines high bandwidth video and multi-channel digital audio into a single cable, and provides crystal clear image resolution.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

## Certifications, Reports and Compatibility



## Applications

- HDMI installations where cable needs to be run through air ducts and plenums, where CMP fire rating is required (educational or commercial installations, etc.)
- Connecting high-definition A/V devices such as Blu-Ray Disc players, HDTVs, DVD Players, DVRs, game consoles, projectors etc.

## Features

- HIGH SPEED HDMI CABLE: 35 ft (10.7 m) HDMI 1.4b Cable with Ethernet supports 4K (3840x2160p, 24, 25, 30Hz 4096x2160p, 24Hz), Full HD (1920x1080p, 120Hz), 10.2 Gbps bandwidth, wide aspect ratio, 8Ch Audio (5.1/7.1/DD+/Dolby TrueHD), 3D Video
- DURABLE PLENUM RATED CABLE: Ultra HD fully molded HDMI cable with durable PVC jacket and strain relief for high strength and reliability; CMP fire rated cable for plenum installs: ducts, walls, conduits, ceilings; Ideal for Commercial environments
- QUALITY CONSTRUCTION: 24AWG wire with gold-plated connectors, and superior EMI shielding with Al-Mylar foil and braid improve signal integrity and reliability, providing higher quality video and audio; Supports HDMI 1.4 and earlier versions
- APPLICATIONS: Use in home offices/boardrooms/conference rooms/offices/classrooms, works with your laptop/professional workstation/soundbar for presentations via UHD/4K monitors, projector or large display; Samsung/Sony/Apple TV/Dell/Lenovo
- SPECS: 35 ft (10.7 m) Black HDMI 1.4b HDMI Cord Male to Male 24 AWG Gold-plated connectors PVC Jacket Shield: Al-Mylar foil with Braid ARC, Deep Color, HDCP 1.4, CEC YCC601 Color CMP Fire Rated

---

### Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	Plenum

---

### Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
Connector B	1 - HDMI (19 pin)

---

### Physical

**Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24 AWG
Cable Length	35.0 ft [10.7 m]
Product Length	35.0 ft [10.7 m]
Weight of Product	3.2 lb [1.4 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	13.1 in [33.4 cm]
Package Width	13.7 in [34.7 cm]
Package Height	1.9 in [4.7 cm]
Shipping (Package) Weight	3.2 lb [1.5 kg]

---

**What's in the Box**

Included in Package	1 - 35 ft Plenum-Rated High Speed HDMI Cable
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

