

2 Port Industrial Wall Mountable USB to Serial Adapter Hub with DIN Rail Clips - TAA

Product ID: ICUSB2322I



The ICUSB2322I 2-Port Industrial USB to Serial Hub with DIN Rail Clips converts a single USB port into two RS232 serial ports, enabling you to connect to, monitor and control your serial devices.

Featuring rugged metal construction, with sturdy wall-mounting brackets and top-hat DIN Rail clips (included), this USB to Serial Hub provides versatile mounting options and a robust solution for both harsh industrial environments and simple desktop installations.

This USB powered adapter also retains assigned serial COM port values once connected, allowing the same values to be automatically reassigned to the ports provided by the adapter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for IT Administrators looking to add legacy functionality to newer notebooks, PCs and servers that lack an integrated RS232 port
- Connect, monitor and control industrial/automotive sensors and equipment
- Connect bar code scanners, receipt printers and other point of sale devices
- Connect a satellite receiver, serial modem, or PDA with serial sync
- Connect and program LED and Digital signage boards with serial communication ports

Features

- 2-port USB to RS232 serial adapter
- Rugged metal construction
- Wall-mountable, with included DIN Rail clips
- COM retention: COM Port assignments maintained across reboot
- Baud Rate up to 921.6 Kbps
- Powered by an available USB port - no external power adapter required

Hardware

Warranty	2 Years
Ports	2
Interface	Serial
Bus Type	USB 2.0
Port Style	External Hub
Chipset ID	FTDI - FT232RL

Performance

Serial Protocol	RS-232
Max Baud Rate	921.6 Kbps
Data Bits	7, 8
FIFO	256 Bytes
Parity	Odd, Even, Mark, Space, None

Stop Bits 1, 2

Connector(s)

 External Ports 2 - DB-9 (9 pin, D-Sub)
 1 - USB B (4 pin)

Software

 OS Compatibility Windows CE (4.2, 5.0, 6.0), XP Embedded, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10, 11, 11 ARM
 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019, 2022, 2025
 macOS 10.6 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1
 Linux Kernel 3.0.x and up - LTS Versions only

Indicators

LED Indicators 2 - Each, Tx/Rx Activity indicators

Power

 Input Voltage 5V DC
 Output Voltage 5 DC
 Plug Type M

Environmental

 Operating Temperature 0C to 55C (32F to 131F)
 Storage Temperature -20C to 85C (-4F to 185F)
 Humidity 5~95% RH

Physical Characteristics

 Color Black
 Material Steel
 Cable Length 6.0 ft [1.8 m]
 Product Length 4.1 in [10.4 cm]
 Product Width 2.6 in [6.6 cm]
 Product Height 0.9 in [2.4 cm]

Weight of Product	5.7 oz [162 g]
-------------------	----------------

Packaging Information

Package Quantity	1
Package Length	8.2 in [20.8 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.7 in [4.3 cm]
Shipping (Package) Weight	12.4 oz [352.0 g]

What's in the Box

Included in Package	1 - USB to RS-232 Serial Adapter
	1 - DIN rail kit
	1 - 6 ft USB A to B cable
	1 - Driver CD
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*