

HPE JD089B Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m - HPE 5820AF, 12500, 5500

**Product ID:** JD089BST



The JD089BST is an HPE JD089B compatible copper transceiver module that has been designed, programmed and tested to work with HPE brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000BASE-T compliant networks, with a maximum distance of up to 100 m (328 ft).

#### Technical Specifications:

- Maximum Data Transfer Rate: 1000 Mbps
- Type: Copper
- Connection Type: RJ45 Connector
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 4,655,371 hours
- Power Consumption: Less than 1.3 Watts
- Digital Diagnostics Monitoring (DDM): No

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

#### Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP modules in HP switches and routers
- Expand your network to remote segments

## Features

- 100% HPE JD089B COMPATIBLE: Works with HPE switches like 5820AF, 12500, 5500, E4800, E4500 and others
- TECHNICAL SPECS: 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in HPE routers and switches
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	Lifetime
Compatible Brand	HPE
Industry Standards	IEEE 802.3i 10BASE-T IEEE 802.3ab 1000BASE-T IEEE 802.3u 100BASE-TX

---

### Performance

Maximum Data Transfer Rate	1000 Mbps
Max Transfer Distance	100m [328ft]
Type	Copper
Fiber Operating Mode	Full-Duplex
DDM	No

---

Compatible Networks	10/100/1000 Mbps
MTBF	4,655,371 hours
Power Consumption (In Watts)	< 1.3 W

---

**Connector(s)**

Local Unit Connectors	1 - RJ-45
-----------------------	-----------

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

---

**Physical Characteristics**

Color	Silver
Product Length	2.7 in [68 mm]
Product Width	0.5 in [1.4 cm]
Product Height	0.5 in [1.4 cm]
Weight of Product	0.9 oz [25 g]

---

**Packaging Information**

Package Length	4.5 in [11.4 cm]
Package Width	3.6 in [9.2 cm]
Package Height	1.3 in [3.3 cm]
Shipping (Package) Weight	1.9 oz [54.0 g]

---

**What's in the Box**

Included in Package	1 - SFP transceiver
---------------------	---------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

*\*Product appearance and specifications are subject to change without notice.*

