

Mobile TV Cart - Portable Rolling TV Stand for 37-70" VESA Display (154lb/70kg) - TV Stand w/Shelf & Storage Compartment - Rotate/Tilt Display - Universal TV Mount on Wheels

Product ID: MBLTVSTNDEC



This Mobile TV Stand enables you to create a mobile media center with displays from 37" to 70" and up to 154lb in weight, making it easier to move your AV equipment across classrooms, offices, or learning environments. For better stability and safety, the mobile cart was engineered with a 0.92m x 0.70m base.

This rolling tv stand with a mount will adapt to the different setups that you may encounter in your office space. You can tilt the viewing angle within 0/+5 to best suit your environments and reduce glare and rotate your display -90/+90 for portrait or landscape orientations.

For increased portability, this universal mobile cart offers a device shelf for equipment that needs to be easily accessible and supports up to 11lb/5kg, and a storage compartment behind the TV ideal for storing equipment like power bars, or media players. To avoid interference with larger displays in portrait mode, the equipment shelf protrudes out from the back.

The heavy-duty TV stand's durable construction makes it ideal for commercial use, in environments with multiple users and frequent movement between areas. Additionally, it is equipped with 4 polyurethane casters which are lockable using a pedal and will provide smooth movement across different types of floors/carpet, while avoiding drag marks on surfaces. Built-in cable management keeps your cables organized and hidden from view; cables are run through the columns with entry points below the storage compartment.

The MBLTVSTNDEC mobile TV cart stand is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Roll the cart between boardrooms, classrooms, or other spaces
- Share media equipment and minimize costs
- Set up a stationary display during special events
- Set up a permanent display in areas where you can't wall mount

Features

- **HEAVY DUTY PORTABLE TV CART:** Durable mobile TV cart for 37-70 inch displays (154lb/70kg); 4 smooth-rolling polyurethane lockable casters/wheels to avoid drag marks; Sturdy steel base to prevent tipping
- **EASILY ADJUSTABLE:** Movable rolling TV stand/cart positions the center of your display at 53.9" (137cm) from the floor; Tilt 0/+5; +/-90 rotation allows the display/flat screen to be easily adjusted & locked in portrait or landscape position
- **EQUIPMENT SHELF & STORAGE:** Mobile TV stand with a single shelf that supports devices (media player, laptop, etc.) up to 11lb (5kg), & an enclosed compartment behind the TV for storing equipment like power bars/media players Shelf size 16.5"x11.4"/42x29cm
- **DISPLAY COMPATIBILITY:** Universal television mount support TVs and interactive displays; Compatible w/ brands LG, Samsung, Sony & Sharp; Supports VESA patterns 200x200, 300x300, 350x350, 400x200, 400x300, 400x400, 600x200, 600x400; Screws/spacers incl.
- **ORGANIZE YOUR PRESENTATION CART:** Mobile TV cart/trolley features integrated cable management to keep cables organized running through each column; Enclosed compartment to hide equipment; incl. cable clip holders & reusable cable clips to organize setup

Hardware

Warranty	2 Years
# of Displays Supported	1
Mounting Options	Mobile Cart
VESA Hole Pattern(s)	200x200 mm
	300x300 mm
	350x350 mm
	400x200 mm
	400x300 mm

400x400 mm

600X200 mm

600x400 mm

Performance

Minimum Display Size	37"
Maximum Display Size	70"
Fits Curved Display	Yes
Video Wall	No
Height Adjustment	No
Display Tilt	0 / +5
Display Rotation	90

Physical Characteristics

Color	Black
Product Length	27.6 in [70.2 cm]
Product Width	36.2 in [92.0 cm]
Product Height	62.8 in [159.5 cm]
Weight of Product	52.5 lb [23.8 kg]

Packaging Information

Package Quantity	1
Package Length	34.2 in [86.9 cm]
Package Width	3.4 ft [1.0 m]
Package Height	6.1 in [15.4 cm]
Shipping (Package) Weight	56.0 lb [25.4 kg]

What's in the Box

Included in Package	1 - Base
---------------------	----------

- 4 - Casters
- 2 - Base Columns
- 2 - Upper Columns
- 1 - Equipment Shelf
- 2 - Shelf Brackets
- 1 - Front Bracket Cover
- 1 - VESA Mounting Plate
- 1 - Rear Bracket Cover
- 2 - VESA Extension Arms (L)
- 2 - VESA Extension Arms (R)
- 4 - Cable Covers
- 8 - M8x20mm Screws
- 8 - M6x8mm Screws
- 16 - M6x12mm Screws
- 1 - M6x18mm Screw
- 8 - M8x8mm Screws
- 5 - Cable Clip Holders
- 5 - Cable Clips
- 1 - M6 Wrench
- 1 - M10 Wrench
- 1 - 4mm Hex Key
- 1 - 5mm Hex Key
- 4 - M5x14mm Screws
- 4 - M6x14mm Screws
- 4 - M6x30mm Screws
- 4 - M8x30mm Screws



4 - M8x50mm Screws

4 - Washers

8 - Small Spacers

1 - Large Spacers

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

