

6ft (1.8m) Mini DisplayPort to DVI Cable - Mini DP to DVI Adapter Cable - 1080p Video - Passive
mDP to DVI-D Single Link, mDP or Thunderbolt 1/2 Mac/PC to DVI Monitor/Display

Product ID: MDP2DVIMM6



The MDP2DVIMM6 6-foot Mini DisplayPort to DVI Cable is a cost-effective Mini DisplayPort to DVI link that lets you connect a DVI monitor to a PC or Mac with a Mini DisplayPort output - saving the expense of upgrading the monitor for compatibility. This Mini DisplayPort adapter is the perfect accessory for any of your MacBook or Microsoft Surface Pro devices with mDP. This all-in-one, easy to use Mini DisplayPort/DVI cable requires no additional converters or adapters, and no driver or software installation.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port.

MDP2DVIMM6 is a passive adapter that requires a DP++ port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep your existing DVI display with our Mini DisplayPort to DVI video converter cables
- Use a DVI monitor with DisplayPort equipped MacBook's and iMac's with Mini DisplayPort video output

Features

- **MINI DISPLAYPORT TO DVI CABLE:** 6ft (1.8m) Mini DisplayPort 1.2 (HBR2) to DVI-D (digital only) single-link cable connects a DVI display 1080p 60Hz or 4K 30Hz (monitor w/ HDMI clock rate); EDID pass-through ensures compatibility between source & display
- **HOST COMPATIBILITY:** Passive video converter supports mDP++ source including Thunderbolt 1 & 2 MacBooks, MacBook Air & Mac Mini, Microsoft Surface Pro 1-6, desktops (AMD FirePro/NVidia Quadro), laptops, mini itx computers, Intel NUC & docks
- **INTEGRATED DISPLAY CABLE:** Mini DisplayPort to DVI adapter cable has slim & flexible design with adapter chip built into DVI connector reducing clutter & providing a tidy install in the office, boardroom or home office
- **INCREASE PRODUCTIVITY:** Connect a DVI monitor or projector, or add a second display to your workstation using the mDP to VGA display adapter cable. Supports DVI screw locking cable to prevent accidental disconnection mDP Male to DVI Male
- **EASY TO USE:** With no software or drivers required, the Mini DP to DVI converter cable/cord works with any OS including Windows, Ubuntu and macOS; Compatible with MiniDP devices like TB1/TB2 MacBooks with Mini DisplayPort

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No

Performance

Maximum Cable Length	6.0 ft [1.8 m]
Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	DVI - No Audio Support

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - DVI-D (25 pin)

Special Notes / Requirements

System and Cable Requirements	DP++ (DisplayPort++) port required on video card or video source for DVI and HDMI signal pass-through.
-------------------------------	--

Environmental

Operating Temperature	0C to 35C (32F to 95F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	5%-80% RH (no condensation)

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.4 in [3.6 cm]
Product Height	0.7 in [1.7 cm]
Weight of Product	3.0 oz [84.0 g]

Packaging Information

Package Quantity	1
Package Length	5.9 in [15.1 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.9 in [2.4 cm]
Shipping (Package) Weight	3.2 oz [92.0 g]

What's in the Box

Included in Package	1 - 6 ft Mini DisplayPort to DVI Cable - M/M
---------------------	--

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*