

Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA DVI or HDMI Converter

Product ID: MDP2VGDVHD



This travel adapter lets you connect your mDP enabled Ultrabook or laptop computer to any VGA or HDMI display.

Backed by rigorous testing to ensure compatibility, the 3-in-1 Mini DisplayPort adapter is the perfect accessory for any of your Microsoft Surface Pro devices that are equipped with mDP.

Why carry multiple adapters when you only need one? Instead of keeping three different adapters on-hand, the mDP travel adapter offers VGA, DVI and HDMI outputs, so you'll be able to connect from your laptop mDP output to any modern boardroom or classroom display -- an ideal plug-and-play solution for BYOD (Bring Your Own Device) applications at the office.

Plus, because the converter supports video resolutions up to 1920x1200 or 1080p you can convert a Mini DisplayPort video source to HDMI, VGA or DVI without sacrificing video quality.

The travel A/V adapter maximizes portability with a small footprint and lightweight design. The convenient design ensures the adapter is as portable as your laptop, fitting easily into your laptop bag or carrying case and eliminates the need to carry more than one adapter. With this adapter you can walk into virtually any boardroom ready to present, making a great first impression, and saving you the embarrassment of having to rummage through your bag looking for the right connector.

The 3-in-1 converter is compatible with the Intel Thunderbolt port on your computer and installs easily with no software or drivers required.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD laptop/Ultrabook to a provided HDMI, DVI, or VGA display at work
- Connect a DVI, VGA, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

Features

- **3-IN-1 DISPLAY ADAPTER:** Seamlessly connect a Mini-DisplayPort source to virtually any display with a single adapter; Supports mDP to HDMI, DVI, or VGA (only one output active at a time); 7.1 channel surround sound over HDMI for high-fidelity AV setups
- **VIDEO RESOLUTIONS:** This travel video adapter supports up to 4K at 30Hz via HDMI output and up to 1920x1200/1080p via DVI and VGA outputs; Designed for versatile deployments across modern and legacy display environments
- **PLUG-AND-PLAY:** OS-independent adapter requires no drivers or software, ideal for quick deployments across Windows, macOS, and Linux systems without IT overhead
- **TRAVEL-READY DESIGN:** This A/V adapter features a lightweight, compact design that fits effortlessly into laptop bags or technician field kits; Ideal for both mobile setups, permanent desktop workstations and IT professionals on the go
- **TECHNICAL SPECIFICATIONS:** Unidirectional design (only converts from a Mini-DisplayPort source to an HDMI/DVI/VGA monitor); HDMI/DVI passive ports; VGA active port; Cable Length 5.9in (15cm); Color: Black

Hardware

Warranty	3 Years
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-D - Single-Link
	HDMI - 1.4
	VGA
Audio	Yes

Performance

Maximum Cable Distance To Display	49.9 ft [15.2 m]
Maximum Analog Resolutions	1920x1200/1080p
Maximum Digital	1920x1200/1080p

Resolutions

Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support
	HDMI - 7.1 Channel Audio
	VGA - No Audio Support

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - HDMI (19 pin)
	1 - VGA (15 pin, High Density D-Sub)
	1 - DVI-D (25 pin)

Special Notes / Requirements

Note	<p>Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.</p> <p>The HDMI port is a passive port.</p> <p>The DVI-D is a passive port.</p> <p>The VGA port is an active port.</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	--

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	10~85% RH

Physical Characteristics

Color	Black
Cable Length	5.9 in [150 mm]
Product Length	10.6 in [27.0 cm]

Product Width	1.8 in [4.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	2.0 oz [57.0 g]

Packaging Information

Package Quantity	1
Package Length	6.4 in [16.2 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.9 in [2.4 cm]
Shipping (Package) Weight	2.6 oz [74.0 g]

What's in the Box

Included in Package	1 - Mini DisplayPort to HDMI/VGA/DVI Adapter
	1 - Installation Guide

Warranty Information

Warranty	3 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

