

4-Port DisplayPort 1.2 Splitter, DisplayPort to 4x DP Multi-Monitor Adapter, Quad 1080p 60Hz Computer MST Hub - Windows Only, No Drivers

**Product ID:** MSTDP124DP



This MST hub lets you connect four monitors to your DisplayPort (DP) 1.2 equipped Windows laptop or desktop.

The newest generations of computers are more portable than ever, which often means that you're left with fewer video outputs and smaller integrated screens. This MST hub solves both of these problems by letting you connect four additional displays to your computer, which makes multitasking much easier.

With the MST hub, you can use DisplayPort video adapters and cable adapters that enable you to connect HDMI, VGA or DVI displays. This ensures your MST hub will be compatible with virtually any television, monitor or projector. This MST hub is VESA and DisplayPort certified to support DP 1.2 enabled systems, for seamless integration with your existing video equipment.

Using the MST hub, you can extend your desktop onto additional monitors and stream independent content to each display giving you the freedom to multitask and increase your productivity. You can also mirror the same image onto multiple displays for remote viewing applications such as digital signage.

MST technology uses your existing video card to minimize the use of system resources while delivering Ultra HD 4K resolutions. This unprecedented performance makes MST perfect for high-resolution applications such as graphic design, gaming and medical imaging.

The MSTDP124DP supports plug-and-play installation for a hassle-free setup, and is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility





## Applications

- Build a four display video wall to present entertainment to your patrons with an impressive display at a restaurant or shopping center
- Use one screen for reference data such as websites, while composing a report on another screen
- Dock your DP 1.2 device and add four high-resolution displays to your workstation
- Create a panoramic video wall for DisplayPort digital signage applications
- Edit images, video or audio clips across four additional displays in any orientation or resolution
- Perfect for spanning a spreadsheet/worksheet across additional displays, to avoid side-scrolling

## Features

- **MULTI-MONITOR CONFIGURATION:** Quad-Monitor DisplayPort 1.2 MST Hub drives up to 4x 1080p 60Hz DisplayPort monitors using a DP video port on a Windows desktop PC or laptop; Not compatible with macOS
- **NO DRIVERS OR SOFTWARE:** Increase productivity by adding four extended or mirrored displays to a Windows computer; Utilize integrated or discrete GPU (Intel/AMD/Nvidia) capabilities enabling high performance graphics with minimal CPU usage
- **HARDWARE COMPATIBILITY:** Host system must support DP 1.2 / HBR2 / MST; Please verify maximum number of displays supported by your GPU; Some GPU chips (such as Intel HD Graphics) are only capable of supporting a maximum of three displays;
- **EASY TO USE:** Extend your desktop at your workstation in the office/home office; Latching DisplayPort connector ensures a reliable connection and prevents accidental disconnection; Not compatible with HDMI output ports; Universal Power Adapter included
- **OUR ADVANTAGE:** Included connectivity tools for IT Pro's and IT help-desk support teams with Windows Layout Utility which restores windows app locations when re-connecting the 4-Port DisplayPort Multi-Monitor Adapter

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
Ports	4

---

AV Output	DisplayPort - 1.2
Audio	Yes
Chipset ID	MegaChips - STDP4320

---

**Performance**

Maximum Cable Distance To Display	6.6 ft [2 m]
Maximum Digital Resolutions	3840 x 2160 @30hz
Supported Resolutions	1024x768 1280x720 (High-definition 720p) 1920x1080 (High-definition 1080p) 1920x1200 2560x1440 2560x1600 3840 x 2160 (Ultra HD 4K) @30hz
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 5.1 Channel Audio

---

**Connector(s)**

Connector A	1 - DisplayPort (20 pin)
Connector B	4 - DisplayPort (20 pin)

---

**Software**

OS Compatibility	Windows 11 Windows 10 (32/64) Windows 8/8.1 (32/64) Windows 7(32/64)
------------------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.5 A

---

Output Voltage	5 DC
Output Current	3A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	15

---

#### Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-20C to 70C (-4F to 158F)

---

#### Physical Characteristics

Color	Black
Material	Plastic
Cable Length	7.5 in [19 cm]
Product Length	11.8 in [30.0 cm]
Product Width	4.1 in [10.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	4.6 oz [129.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	6.1 in [15.4 cm]
Package Width	9.6 in [24.5 cm]
Package Height	2.6 in [6.6 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

---

#### What's in the Box

Included in Package	1 - 4-Port Multi Monitor DisplayPort MST Hub  1 - Universal power adapter (NA/EU/UK/AUS)
---------------------	--

1 - Quick install guide

---

**Warranty  
Information**

Warranty	3 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

