

## 6 ft Monitor VGA Cable - HD15 M/M

**Product ID:** MXT101MM



This 6-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our 6ft Coax VGA Cable (MXT101MMHQ).

MXT101MM is backed by a StarTech.com lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

### Features

- Supports low resolution applications
- Guaranteed reliability

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

**Connector(s)**

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

**Special Notes / Requirements**

Note	Pin number 9 is not populated on these connectors
------	---

**Physical Characteristics**

Color	Gray
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Cable OD	0.2 in [5.3 mm]
Product Length	6.0 ft [1.8 m]
Product Width	1.3 in [3.3 cm]
Product Height	0.7 in [1.8 cm]
Weight of Product	4.3 oz [122 g]

**Packaging Information**

Package Quantity	1
Package Length	6.4 in [16.2 cm]
Package Width	5.0 in [12.7 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	4.6 oz [130.0 g]

**What's in the Box**

Included in Package	1 - 6 ft VGA Monitor Cable - HD15 M/M
---------------------	---------------------------------------

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

