

## 10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M

**Product ID:** MXT101MMLP10



The MXT101MMLP10 10-foot, Low Profile High Resolution Monitor VGA Extension Cable, is designed to provide the highest video quality available through VGA. This super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality High Resolution Monitor VGA Cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Replacement VGA/SVGA monitor cable
- Lightweight video cable for laptop
- Ideal for high resolution monitors (1024x768 and above)

### Features

- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

**Physical Characteristics**

Color	Black
Wire Gauge	32 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	5.3 oz [149 g]

---

**Packaging Information**

Package Quantity	1
Package Length	7.3 in [18.6 cm]
Package Width	5.0 in [12.7 cm]
Package Height	1.1 in [2.9 cm]
Shipping (Package) Weight	7.3 oz [206.0 g]

---

**What's in the Box**

Included in Package	1 - 10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M
---------------------	--

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

