

## USB Crash Cart Adapter with File Transfer & Video Capture - TAA

**Product ID:** NOTECONS02



The USB crash cart adapter gives you control of a headless system, turning your laptop into a portable crash cart for rack servers, PCs, ATMs, kiosks, and more.

Simply connect the laptop crash cart adapter to your computer using the included USB cable, then connect the integrated USB and VGA cables to your server for instant BIOS-level control. With no server-side software required, you can be up and running instantly.

\*Please note that the mouse function may be limited in some BIOS/UEFI environments

With the flexible software interface, you can transfer files from your laptop to the server, capture videos for records or instructional purposes, take screenshots and scale the display window to full screen mode or smaller, with no scroll bars helping you to troubleshoot faster.

Powered from the server-side USB connection, the KVM adapter doesn't require an AC outlet so you can connect to any PC or device that has a VGA and USB port, even if there's no power outlet available.

This pocket-sized adapter features a compact design that easily fits inside your laptop bag and requires no additional accessories to connect, eliminating the need to lug around a large, awkward traditional crash cart to troubleshoot and service your systems.

StarTech.com offers a wide selection of high-quality KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

## Certifications, Reports and Compatibility





## Applications

- ATM and VLT maintenance and repair
- Mobile systems and server repair

## Features

- LAPTOP TO SERVER: USB crash cart adapter connects your laptop to a headless system, turning your laptop into a portable console for rack servers in your server room, PCs, ATMs, kiosks, etc
- EFFICIENT TROUBLESHOOTING: Easily transfer files, capture screenshots, and log activity using the crash cart adapter software; For optimal performance, install the latest drivers making sure to download the drivers specifically for the NOTECONS02
- BIOS-LEVEL CONTROL: Connect the crash cart adapter to your laptop using the included USB cable, then connect the integrated USB & VGA cables to your server for instant BIOS-level control; Note: Mouse function may be limited in some BIOS/UEFI environments
- SELF-POWERED: The KVM adapter is powered by the server-side USB connection, reducing strain on the laptop's battery and eliminating the need for an AC outlet, allowing you to connect to any PC or device with a VGA output port and USB connection
- COMPACT DESIGN: This TAA Compliant pocket-sized data center crash cart adapter requires no additional accessories, eliminating the need to carry around a traditional crash cart/trolley when troubleshooting and servicing your systems

---

### Hardware

Warranty	2 Years
Audio	No
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1

---

Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

**Performance**

On-Screen Display	No
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	1920x1200 @ 60Hz
Maximum Number of Users	1
MTBF	909000

---

**Connector(s)**

Console Interface(s)	1 - USB Mini-B (5 pin)
Host Connectors	1 - VGA (15 pin, High Density D-Sub)
	1 - USB 2.0 Type-A (4 pin, 480Mbps)

---

**Software**

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11  Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019, 2022, 2025  macOS 10.9 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1  Linux 2.6 and up - LTS Versions only
------------------	--

---

**Special Notes / Requirements**

Note	<ul style="list-style-type: none"> <li>- If you're interfacing with a Linux device, this adapter is only compatible with standard QWERTY keyboards in U.S English configuration</li> <li>- Note: Mouse function may be limited or non-functional in some BIOS/UEFI environments</li> </ul>
------	--

---

**Indicators**

LED Indicators	1 - User Console/USB Link
----------------	---------------------------

1 - Host/Server Video (VGA) Link

1 - Host/Server Keyboard/Mouse USB Link

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	80% RH

---

**Physical Characteristics**

Color	Black
Material	Plastic
Cable Length	16.4 in [416 mm]
	1 x 15in (385mm) USB host cable
	1 x 11in (290mm) VGA host cable
	1 x 6ft (1.8m) USB Console cable
Product Length	5.2 in [13.3 cm]
Product Width	2.9 in [7.4 cm]
Product Height	0.6 in [1.5 cm]
Product Depth	4.5 in [115 mm]
Weight of Product	6.0 oz [170.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	11.9 in [30.1 cm]
Package Width	6.5 in [16.5 cm]
Package Height	2.2 in [5.5 cm]

Shipping (Package) 12.6 oz [358.0 g]  
Weight

---

**What's in the Box**

Included in Package	1 - USB Crash Cart Adapter
	1 - USB A to Mini-B Cable

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

