

10ft (3m) Heavy Duty Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, NEMA 5-15R to NEMA 5-15P AC Power Cord - UL Listed

Product ID: PAC1011410



The PAC1011410 Computer Power Cord Extension Cable features a heavy gauge wire (14 AWG) that is suitable for handling high power loads, making it a reliable solution for connecting larger servers to PDU (Power Distribution Units).

This 10ft power extension cable extends your existing power connection by 10ft, enabling you to use the PC or another powered device at a greater distance from the power source/outlet.

This high quality replacement Power Extension Cord is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend an existing power cord by an additional 10ft
- StarTech.com's computer power extension cord saves space and conveniently connects large power adapters so you can maximize all your power/surge strip outlets

Features

- **HEAVY DUTY EXTENSION CORD:** This 10ft (3m) 14AWG universal power cord with NEMA 5-15R to NEMA 5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 10ft (3m) AC Power Cord NEMA 5-15R to NEMA 5-15P 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Performance

Maximum Cable Length	10.0 ft [3.0 m]
----------------------	-----------------

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]

Product Length	10.0 ft [3.0 m]
Product Width	1.0 in [2.5 cm]
Product Height	1.4 in [3.5 cm]
Weight of Product	16.9 oz [478.0 g]

Packaging Information

Package Quantity	1
Package Length	11.0 in [28.0 cm]
Package Width	4.6 in [11.7 cm]
Package Height	2.7 in [6.9 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 10 ft 14 AWG Power Cord Extension - NEMA 5-15R to NEMA 5-15P
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

