

1ft (30cm) Short Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

**Product ID:** PAC101



This 12in Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 12in of reach for your monitor, computer case, or any other powered device.

## Certifications, Reports and Compatibility



## Applications

- Allows you to attach bulky power adapter to a power strip or a wall outlet without blocking other outlets
- StarTech.com's power extender cable saves space and conveniently connects big sized adapters so you can maximize all your power/surge strip outlets

## Features

- POWER EXTENSION CORD: This 1ft (0.3m) 16AWG AC power extension cable with NEMA 5-15R and NEMA

5-15P connectors is suitable for workstations/home office - Indoor use - Rated to carry 125V at 13A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) - Fully molded strain relief on connectors for durability - Fire Rating: VW-1 - 3 Conductor extension cord with 100% copper wire - This cable is available in other lengths
- **SPECS:** 1ft (0.3m) AC Power Cord - NEMA 5-15R to NEMA 5-15P - 16AWG - 125V 13A (Max) - Jacket Type: SJT - Jacket Material: PVC - Black - Temperature Range: 37F to 140F (3C to 60C) - Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets - Extend a 3-prong power connection from your desktop computer, server, or printer - Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

#### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

---

#### Power

Input Voltage	125 AC
Input Current	13 A

---

#### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
-----------------------	---------------------------

---

#### Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	12.0 in [304.8 mm]
Product Length	12.0 in [30.5 cm]
Product Width	1.0 in [2.5 cm]

Product Height 2.1 in [5.5 cm]

Weight of Product 3.0 oz [86.0 g]

---

**Packaging Information**

Package Quantity 1

Package Length 5.5 in [14.0 cm]

Package Width 7.8 in [19.8 cm]

Package Height 1.1 in [2.8 cm]

Shipping (Package) Weight 4.9 oz [138.0 g]

---

**Warranty Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

