

1.5ft (45cm) Power Extension Cord, Flat NEMA 5-15P to NEMA 5-15R, 10A 125V, 18AWG, Black
Computer Power Extension Cord, Flat Plug Extension Cord, AC Outlet Extension Cable, UL Listed

Product ID: PACF10118IN



This power extension cord features a flat, low-profile plug that sits flush against the outlet on your power strip, surge protector or wall outlet. The flush connection saves space and lets you attach bulky power adapters without blocking other available power outlets.

Plus, the NEMA cord also lets you extend an existing power cord by up to 1.5 feet. The added cable distance lets you minimize clutter, giving you more room for additional connections on your power strip, surge protector or wall outlet.

The PACF10118IN is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Save space on your power strip, surge protector or wall outlet

Features

- **AC POWER EXTENSION CORD:** This 18in (0.45m) 18AWG AC power extension cable with NEMA 5-15R and Flat NEMA 5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability

Fire Rating: VW-1 3 Conductor extension cord with 100% copper wire. This cable is available in other lengths.

- SPECS: 18in (0.45m) AC Power Cord NEMA 5-15R to Flat NEMA 5-15P 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)
- COMPATIBILITY: PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10A

Physical Characteristics

Color	Black
Connector Style	Flat to Straight
Wire Gauge	18 AWG
Cable Length	1.5 ft [0.5 m]
Product Length	18.0 in [45.7 cm]
Product Width	1.3 in [3.4 cm]
Product Height	1.7 in [4.3 cm]

Weight of Product	3.3 oz [94.0 g]
-------------------	-----------------

Packaging Information

Package Quantity	1
Package Length	11.4 in [29.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.0 in [2.5 cm]
Shipping (Package) Weight	3.5 oz [100.0 g]

What's in the Box

Included in Package	1 - NEMA 5-15P to NEMA 5-15R power cord
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*