

Wireless Presentation Remote with Green Laser Pointer - 90 ft. (27 m) - TAA

Product ID: PRESREMOTEG



This wireless presentation remote lets you engage your audience, draw their attention and control your presentation. It's ideal for presenting in large lecture halls, or conference centers.

With a built-in green laser pointer, the presentation remote lets you guide your audience's attention to critical information in your content. It's perfect for PowerPoint presentations, websites or any other documents you want to share.

The green laser works on surfaces where red lasers won't display. It appears nicely on bright projector or LCD/LED HD screens.

The presentation clicker features a wireless range of 90 ft. (27 m). It gives you control of what's on the screen throughout the room, and the freedom to move around and present as if you were at your computer.

You can:

Navigate through your slides

Black out the screen to focus your audience's attention solely on you or something else in the room

Control the volume of a video

The remote features a sleek, ergonomic design and includes the required batteries along with a protective carrying case, for total portability. You can store the wireless receiver inside the presentation remote when you're not using it and the remote will automatically power off.

The USB receiver works with virtually any Mac or Windows computer. Simply plug the receiver into your laptop and you're ready to present.

The PRESREMOTEG is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control your PowerPoint presentation with easy-to-use buttons
- Highlight critical information with the laser pointer
- Freely move around the room while you present

Features

- Draw your audience's attention to specific on-screen content, using the built-in laser pointer
- The vibrant green colored laser produces a higher visibility on projectors and LCD/LED HD screens than traditional red colored pointers
- Engage your audience, move around the room, with a wireless range of up to 90 ft. (27 m)
- Easily control your presentation with intuitive push-button operation and no additional software or drivers required
- Present from anywhere, the remote comes with a carrying case and fits nicely inside a laptop bag

Performance

Warranty	2 Years
Max Distance	27m [89ft]
General Specifications	Wireless Band: 2.4 GHz
	WAVELENGTH: 532 10nm
	Max Optical Power: 1mW

Connector(s)

Connector Type(s)	1 - USB 2.0 Type-A (4 pin, 480Mbps)
-------------------	-------------------------------------

Special Notes / Requirements

Note	This is a Class 2 Laser Product
------	---------------------------------

Indicators

LED Indicators	1 - Activity (Remote)
----------------	-----------------------

Environmental

Operating Temperature	5 to 45 (41F to 113F)
Storage Temperature	5 to 45 (41F to 113F)
Humidity	30%~80% RH

Physical Characteristics

Color	Black
Product Length	5.3 in [13.4 cm]
Product Width	1.2 in [3.1 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	1.5 oz [43.0 g]

Packaging Information

Package Length	7.6 in [19.4 cm]
Package Width	3.9 in [9.9 cm]
Package Height	1.9 in [4.8 cm]
Shipping (Package) Weight	6.8 oz [192.0 g]

What's in the Box

Included in Package	1 - Presentation Remote
	2 - AAA Batteries
	1 - Carrying Case
	1 - User Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*