

10ft (3m) Heavy Duty Extension Cord, IEC 320 C14 to IEC 320 C13 Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C14 to IEC 320 C13 AC Power Cord - UL Listed

Product ID: PXT1001410



The PXT1001410 Power Cord Extension Cable's heavy-duty (14 AWG) wire gauge is more than sufficient for handling higher power loads, making it a reliable solution for connecting larger servers to PDUs (Power Distribution Units).

This 10-foot Power Extension Cable features one computer power female connector and one hooded male power connector, enabling you to extend the connection between your PC and monitor by up to 10ft.

This high quality replacement Power Extension Cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Make a reliable power connection from your server to a PDU
- Extend the connection between your PC and monitor by up to 10ft
- Saves space and removes clutter, enabling you to place your PC and monitor as needed

Features

- **HEAVY DUTY EXTENSION CORD:** This 10ft (3m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C13 connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 10ft (3m) AC Power Cord IEC 60320 C14 to IEC 60320 C13 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C14 works with North American cables Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C14 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.1 in [2.9 cm]

Product Height	0.8 in [2 cm]
Weight of Product	16.2 oz [458.6 g]

Packaging Information

Package Quantity	1
Package Length	10.8 in [27.4 cm]
Package Width	3.3 in [8.4 cm]
Package Height	1.9 in [4.8 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 10 ft 14 AWG Computer Power Cord Extension - C14 to C13
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

