

6ft (1.8m) Heavy Duty Extension Cord, IEC 320 C14 to IEC 320 C13 Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C14 to IEC 320 C13 AC Power Cord - UL Listed

Product ID: PXT100146



The PXT100146 Power Cord Extension features 14 AWG wire capable of high power connections, making it a reliable solution for connecting large servers to PDU (Power Distribution Units).

This durable Power Extension Cable features one computer power female connector and one hooded male power connector, letting you extend the connection between your PC and monitor by up to 6ft.

Backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Extend the power connection from your server to a PDU by up to 6ft
- Extend the connection between your PC and monitor by up to 6ft
- Saves space and removes clutter, enabling you to place your PC and monitor as needed

Features

- **HEAVY DUTY EXTENSION CORD:** This 6ft (1.8m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C13 connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 6ft (1.8m) AC Power Cord IEC 60320 C14 to IEC 60320 C13 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C14 works with North American cables Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - IEC 60320 C13 Power
Connector B	1 - IEC 60320 C14 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]

Weight of Product 10.1 oz [287.0 g]

Packaging Information

Package Quantity	1
Package Length	11.4 in [29.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.5 in [3.9 cm]
Shipping (Package) Weight	10.2 oz [290.0 g]

What's in the Box

Included in Package	1 - 6ft 14 AWG Computer Power Cord Extension - C14 to C13
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***

