

6ft (1.8m) Heavy Duty Power Cord, NEMA 5-15P to C13 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C13 Power Cord - PC Power Supply Cable

Product ID: PXT101146



The PXT101146 Computer Power Cord features 14 AWG wire capable of high power connections, making it a reliable solution for connecting large servers to PDU (Power Distribution Units).

This durable, universal power cord can be used as a cost-effective replacement for your existing PC power cord, or for plugging a monitor, PC, or laser printer into a grounded power outlet.

StarTech.com's 6ft Computer Power cable lets you plug a monitor, PC, or laser printer into a grounded power outlet and is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connecting large servers to a PDU
- Extend the connection between your PC and monitor by up to 6ft
- Saves space and removes clutter, enabling you to place your PC and monitor as needed

Features

- **HEAVY DUTY AC POWER CORD:** This 6ft (1.8m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstations/home office use. Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire. This C13 thick gauge computer power cord is available in other lengths
- **SPECS:** 6ft (1.8m) AC Power Cord NEMA 5-15P to IEC 60320 C13 14AWG 125V 15A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.3in (7.6mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets. IEC C13 connector works with most desktop computers, servers, monitors, PDUs, printers, and more. Replacement PC power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Cable Length	6.0 ft [1.8 m]
----------------------	----------------

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]

Product Length	6.0 ft [1.8 m]
Product Width	1.0 in [2.5 cm]
Product Height	0.9 in [2.4 cm]
Weight of Product	10.2 oz [290.0 g]

Packaging Information

Package Quantity	1
Package Length	11.4 in [29.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.2 in [3.0 cm]
Shipping (Package) Weight	10.4 oz [296.0 g]

What's in the Box

Included in Package	1 - 6ft 14 AWG Computer Power Cord - NEMA5-15P to C13
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

