

6ft (1.8m) Computer Power Cord, NEMA 5-15P to Right Angle C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable -
UL Listed

Product ID: PXT101L



This 6ft Right Angle Power Cord features a standard NEMA 5-15P connector as well as a right-angled C13 connector allowing you to plug a monitor, PC, or laser printer into a grounded power outlet.

The right angle C13 connector positions the shaft of the cable flush with the back of the device you are connecting, saving space at the connection point. Backed by Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Plugs monitor, PC, or laser printer into a grounded power outlet
- CSA approved

Features

- AC POWER CORD: This 6ft (1.8m) 18AWG flexible computer power cable with NEMA 5-15P and Right-Angle IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- PERFORMANCE AND SAFETY: UL listed (UL62 & UL817) Fully molded strain relief connectors for durability

Conductor Power Cable made from 100% Copper Wire Fire Rating: VW-1

- SPECS: 6ft (1.8m) Power Cable NEMA 5-15P to Right-Angle IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.25in (6.3mm)
- COMPATIBILITY: NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C13 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10A

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.7 in [4.4 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	5.4 oz [152.0 g]

**Packaging
Information**

Package Quantity	1
Package Length	7.9 in [20.1 cm]
Package Width	3.1 in [8.0 cm]
Package Height	1.4 in [3.5 cm]
Shipping (Package) Weight	5.9 oz [166.0 g]

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

