

6ft (1.8m) Laptop Power Cord, NEMA 1-15P to Right Angle C7, 7A 125V, 18AWG, Laptop Charger Cable, Replacement Power Brick Cable, AC Power Cable, UL Listed - TAA

Product ID: PXT101NB-STRA-6F



The IT Pro's Choice

StarTech.com power cables are designed by IT professionals. We design our products to meet the technical requirements of a wide variety of applications. Our in-house specialists subject our products to multiple rounds of comprehensive testing, designed to emulate real-world operational conditions. Third-party labs test our products to confirm compliance with the latest safety standards.

StarTech.com manufactures standard and heavy-duty power cords, extension cords, medical-grade cords, power splitter cables, and power cords featuring passthrough outlets. These products are produced in various lengths, with a range of connector ends, jacket types, and wire gauges. Our power cable products are chosen by IT professionals worldwide for the following reasons:.

- Certified for performance and safety - Manufactured using UL listed components to meet UL62 and UL817 compliance standards
- Minimized environmental impact and safe disposal through compliance with REACH and RoHS regulations and guidelines
- 100% copper wiring tested for continuity and conductivity to ensure maximum performance and reliability
- Tested in a temperature chamber to ensure reliable performance over a wide range of environmental conditions

Backed for life by StarTech.com, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

Certifications, Reports and Compatibility



Applications

- Replacement power cord for Laptop power bricks
- 2-prong power cord compatible with LED TVs

Features

- **RIGHT ANGLE CHARGER CORD:** 6ft (1.8m) AC Power Cable with NEMA 1-15P to Right Angle IEC 60320 C7 connector is compatible with laptop chargers and power bricks; 90-degree C7 connector enables quick access in tight spaces; Indoor use; Rated for 125V at 7A
- **BUILT FOR PERFORMANCE AND SAFETY:** Made with UL Listed components; VW-1 Fire Rated cable with fully-molded connector strain reliefs for durability; 2-conductor power cable made with 100% copper wire
- **SPECS:** 6ft (1.8m); TAA Compliant; NEMA 1-15P to Right Angle IEC C7; 18AWG; 125V 7A (Max); Jacket Rating: NISPT-2; Jacket Material: PVC; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.29in (7.3mm)
- **COMPATIBILITY:** NEMA 1-15P plug works with North American outlets; IEC C7 connector works with power bricks for laptops/notebooks, monitors, scanners, printers, and more; Replacement laptop power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this laptop charger power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; Available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	2
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	NISPT-2

Connector(s)

Connector A	1 - NEMA 1-15 Power (North America)
Connector B	1 - IEC 60320 C7 Power (Non-polarized)

Power

Input Voltage	125V AC
Input Current	7A

Environmental

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	18 AWG
Material	PVC
Cable OD	0.3 in [7.3 mm]
Product Length	6.0 ft [1.8 m]
Product Width	1.5 in [3.8 cm]
Product Height	0.7 in [1.9 cm]
Weight of Product	4.0 oz [112.0 g]

Packaging Information

Package Length	8.2 in [20.8 cm]
Package Width	2.8 in [7.1 cm]
Package Height	1.3 in [3.4 cm]
Shipping (Package) Weight	4.0 oz [114.0 g]

What's in the Box

Included in Package	1 - 6ft NEMA 1-15P to Right Angle C7 Power Cord
---------------------	---

Warranty Information

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***