

10ft (3m) Computer Power Cord, NEMA 5-15P to 2x IEC 320 C13, 10A 125V, 18AWG, Black
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable -
UL Listed

Product ID: PXT101Y10



This C13 Y-cable lets you plug multiple devices into a single power outlet, to maximize the space on your power strip, surge protector or wall outlet. It's perfect for setting up dual monitor arms.

The cable length from the Y-split is 30 inches on each side. This gives you an extended reach for connecting to two monitors securely, without placing a strain on the cable.

You can also use the power-splitter cable to connect a monitor and computer, or any two devices that have a C13 power connection, to the same outlet.

The PXT101Y10 is built to exact specifications and is fully tested to ensure maximum performance. Plus, the cable is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Power two devices from a single power outlet

Features

- **AC POWER Y CABLE:** This 10ft (3m) 18AWG flexible computer power Y cable with NEMA 5-15P and 2x IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. 3 Conductor Power Y cable made from 100% copper wire. Fire Rating: VW-1
- **SPECS:** 10ft (3m) Power Y cable NEMA 5-15P to 2x IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SVT. Jacket Material: PVC. Color: Black. Temperature Range: 37F to 140F (3 to 60). Y cable Outer Diameter: 0.25in (6.3mm)
- **COMPATIBILITY:** NEMA 5-15P works with North American electrical outlets. IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more. Replacement PC power supply Y cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance. This C13 power cord is available in other lengths

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SVT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	2 - IEC 60320 C13 Power

Special Notes / Requirements

System and Cable Requirements	The cable length from the Y split is 30 inches on each side.
-------------------------------	--

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	10.0 ft [3.0 m]

Product Length 10.0 ft [3.0 m]

Weight of Product 13.1 oz [372 g]

Packaging Information

Package Quantity 1

Package Length 8.2 in [20.9 cm]

Package Width 3.3 in [8.3 cm]

Package Height 2.0 in [5.2 cm]

Shipping (Package) Weight 13.1 oz [372.0 g]

What's in the Box

Included in Package 1 - 10ft NEMA 5-15P to 2x C13

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

