

6ft (2m) Computer Power Cord Y Splitter, NEMA 5-15P to 2x C13, 10A 125V, 18AWG, Black AC Power Splitter Cord, PC Power Supply Cable, Dual Monitor Power Cable - UL Listed

**Product ID:** PXT101Y



Our 6 ft IBM Power Cord lets you plug a monitor, PC, or laser printer into a grounded power outlet.

Backed by StarTech.com's lifetime warranty, this high quality IBM power cable is constructed to provide a durable, reliable connection.

## Certifications, Reports and Compatibility



## Applications

- Connects two monitors, PC's, or laser printers into a grounded power outlet
- Ideal when you're running out of space on your power/surge protector or wall outlets

## Features

- AC POWER CORD: This 6ft (2m) 18AWG flexible computer power cable with NEMA 5-15P and 2x IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- PERFORMANCE AND SAFETY: UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1

- SPECS: 6ft (2m) Power Cable NEMA 5-15P to 2x IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SJT  
 Jacket Material: PVC Color: Black Temperature Range: 37F to 140F (3 to 60) Cable Outer Diameter: 0.3in (7.8mm)
- COMPATIBILITY: NEMA 5-15P works with North American electrical outlets IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance This C13 power cord is available in other lengths

---

**Hardware**

Warranty	Lifetime
Cable Type	SVT

---

**Connector(s)**

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	2 - IEC 60320 C13 Power

---

**Special Notes / Requirements**

Note	UL Listed
------	-----------

---

**Power**

Input Voltage	125 AC
Input Current	10A

---

**Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	9.3 oz [263 g]

---

**Packaging Information**

Package Quantity	1
Package Length	9.1 in [23.1 cm]
Package Width	3.2 in [8.2 cm]

Package Height 2.3 in [5.8 cm]

Shipping (Package) Weight 9.7 oz [274.0 g]

---

#### What's in the Box

Included in Package	1 - 6 ft Standard Y Computer Power Cord NEMA 5-15P to 2x C13
---------------------	--

---

#### Warranty Information

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

