

4ft (1.2m) Heavy Duty Power Cord, NEMA 5-15P to C15 AC Power Cord, 15A 125V, 14AWG, Replacement Computer Power Cord, Monitor Power Cable, NEMA 5-15P to IEC 60320 C15 Power Cord - PC Power Supply Cable

Product ID: PXT515C154



The PXT515C154 4-foot Computer Power Cord features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to NEMA 5-15P Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this 5-15P to C15 power cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Compatible with Cisco, HP and other hardware devices with C15 power connections
- Connect large servers to PDUs, even in high-temperature environments

Features

- **HEAVY DUTY AC POWER CORD:** This 4ft (1.2m) 14AWG universal power cord with NEMA 5-15P and IEC 60320 C15 connectors is suitable for workstations/home office use. Rated to carry 125V at 15A.

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. Fire Rating: VW-1 3 Conductor Power Cable made with 100% Copper Wire. This C15 thick gauge computer power cord is available in other lengths.
- **SPECS:** 4ft (1.2m) AC Power Cord NEMA 5-15P to IEC 60320 C15 14AWG 125V 15A (Max) Jacket Type: SJT. Jacket Material: PVC Black. Temperature Range: 37F to 221F (3C to 105C). Cable Outer Diameter: 0.36in (9.1mm).
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets. IEC C15 connector works with most servers and networking equipment. Replacement PC power supply cable/cord.
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 3-prong power cable is backed for life, including free lifetime 24/5 multilingual technical assistance.

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - IEC 60320 C15 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	4.0 ft [1.2 m]
Product Length	4.0 ft [1.2 m]
Weight of Product	8.0 oz [226 g]

Packaging Information

Package Quantity	1
Package Length	7.0 in [17.9 cm]
Package Width	3.1 in [7.9 cm]
Package Height	2.2 in [5.6 cm]
Shipping (Package) Weight	7.6 oz [216.0 g]

What's in the Box

Included in Package	1 - 4 ft Heavy Duty Computer Power Cord - NEMA5-15P to C15
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

