

3ft (1m) Heavy Duty Extension Cord, IEC 320 C14 to IEC 320 C15 Black Extension Cord, 15A 250V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C14 to IEC 320 C15 AC Power Cord - UL Listed

Product ID: PXT14C153



The PXT14C153 C14 to C15 Power Cord (3 ft) features a C15 connector rated for high-temperature equipment, as well as 14 AWG wire suitable for high power connections - a reliable solution for connecting to C14 Power Distribution Units (PDU) located in switchgear rooms and data center environments, or large server applications that require a higher rated, heavier gauge cable.

Designed and constructed of high quality materials, this C14 to C15 power cable is backed by our Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Connect large server applications to PDUs located in high-temperature environments
- Compatible with Cisco, HP and other hardware devices with C15 power connections

Features

- **HEAVY DUTY EXTENSION CORD:** This 3ft (0.9m) 14AWG universal power cord with IEC 60320 C14 to IEC 60320 C15 connectors is suitable for workstations/home office Indoor use Rated to carry 250V at 15A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability
Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 3ft (0.9m) AC Power Cord IEC 60320 C14 to IEC 60320 C15 14AWG 250V 15A (Max) Jacket Type: SJT
Jacket Material: PVC Black Temperature Range: 37F to 221F (3C to 105C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C14 to C15 works with most computer hardware Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride

Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C15 Power

Power

Input Voltage	250 AC
Input Current	15 A

Environmental

Operating Temperature	-20 to 60C (-4 to 140F)
Storage Temperature	0 to 30C (32 to 86F)
Humidity	<55%RH

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	1.1 in [2.8 cm]

Product Height 0.8 in [2.0 cm]

Weight of Product 6.4 oz [181 g]

Packaging Information

Package Quantity 1

Package Length 3.2 in [8.1 cm]

Package Width 7.9 in [20.0 cm]

Package Height 1.9 in [4.7 cm]

Shipping (Package) Weight 6.4 oz [180.0 g]

What's in the Box

Included in Package 1 - 3ft Computer Power Cord 14 AWG - C14 to C15

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*