

6ft (1.8m) Heavy Duty Extension Cord, IEC 320 C19 to IEC 320 C20 Black Extension Cord, 15A 250V, 14AWG, Heavy Gauge Power Extension Cable, IEC 320 C19 to IEC 320 C20 AC Power Cord - UL Listed

Product ID: PXT19C20146



This C19-to-C20 power cord features 14 AWG wire that's suitable for high-power connections, making it perfect for server applications and connecting to a Power Distribution Unit (PDU).

Plus, you can use the cable to extend the reach of your existing power cord by 6 feet, which gives you the extra distance you need to place your devices according to your server room configuration.

Expertly designed and constructed of high-quality materials, the StarTech.com PXT19C20146 power cord is backed by a lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect your server to a PDU
- Extend the connection between your server and PDU by up to 6 feet

Features

- **HEAVY DUTY EXTENSION CORD:** This 6ft (1.8m) 14AWG universal power cord with IEC 60320 C19 to C20

connectors is suitable for servers or other high-powered equipment; Indoor use; Rated to carry 250V at 15A

- **PERFORMANCE AND SAFETY:** UL listed (UL 62 & UL817); Fully molded strain relief on connectors for durability; Fire Rating: VW-1; 3 Conductor Power cable made with 100% copper wire; Available in other lengths
- **SPECS:** 6ft (1.8m) AC Power Cord; IEC 60320 C19 to C20; 14AWG; 250V 15A (Max); Jacket Type: SJT; Jacket Material: PVC; Black; Temperature Range: 37F to 140F (3C to 60C); Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord C19 to C20 works with North American devices; Extend connections to servers, desktop computers, monitors, printers, and more; Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - IEC 60320 C19 Power
Connector B	1 - IEC 60320 C20 Power

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	15 A

Physical Characteristics

Color	Black
Wire Gauge	14 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.3 in [3.3 cm]

Product Height 1.0 in [2.5 cm]

Weight of Product 11.5 oz [326.0 g]

Packaging Information

Package Quantity 1

Package Length 9.6 in [24.3 cm]

Package Width 3.3 in [8.4 cm]

Package Height 2.2 in [5.5 cm]

Shipping (Package) Weight 12.1 oz [342.0 g]

What's in the Box

Included in Package 1 - 6 ft 14 AWG Computer Power Cord - C19 to C20

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*

