

10ft (3m) Computer Power Cord, Right Angle NEMA 5-15P to C13, 10A 125V, 18AWG, Black  
Replacement AC Power Cord, Printer Power Cord, PC Power Supply Cable, Monitor Power Cable -  
UL Listed

**Product ID:** PXTR10110



This NEMA 5-15P to C13 power cord features a right-angled plug, which positions the connector in such a way that it does not block other available outlets. The cable is especially useful when plugging into a dual AC wall outlet as it frees up the second outlet for another power cord.

The high-quality computer power cord is designed to provide a durable, long-lasting connection to your peripheral devices. It makes a suitable replacement for worn out or missing computer, monitor or printer power cords.

The PXTR10110 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Save space on a two outlet AC wall outlet
- Plug your monitor, computer, or printer into a grounded power outlet
- Dependable replacement or spare computer power cord

## Features

- AC POWER CORD: This 10ft (3m) 18AWG flexible computer power cable with Right-Angle NEMA 5-15P and IEC 60320 C13 connectors is suitable for workstation/home office use. Rated to carry 125V at 10A
- PERFORMANCE AND SAFETY: UL listed (UL62 & UL817) Fully molded strain relief connectors for durability. 3 Conductor Power Cable made from 100% Copper Wire. Fire Rating: VW-1
- SPECS: 10ft (3m) Power Cable Right-Angle NEMA 5-15P to IEC 60320 C13 18AWG 125V 10A (Max) Jacket Rating: SJT. Jacket Material: PVC. Color: Black. Temperature Range: 37F to 140F (3 to 60). Cable Outer Diameter: 0.3in (7.8mm)
- COMPATIBILITY: NEMA 5-15P works with North American electrical outlets. IEC C13 connector works with most desktop computers, and many monitors, scanners, printers, and more. Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance. This C13 power cord is available in other lengths

---

**Hardware**

Warranty	Lifetime
Number of Conductors	3
Cable Type	SJT

---

**Connector(s)**

Connector A	1 - NEMA 5-15 Power (North America)
	1 - IEC 60320 C13 Power

---

**Special Notes / Requirements**

Note	UL Listed
------	-----------

---

**Power**

Input Voltage	125 AC
Input Current	10 A

---

**Physical Characteristics**

Color	Black
Connector Style	Right Angle to Straight
Wire Gauge	18 AWG
Cable Length	10.0 ft [3.0 m]

---

Product Length	10.0 ft [3.0 m]
Product Width	1.1 in [2.7 cm]
Product Height	1.6 in [4.1 cm]
Weight of Product	10.6 oz [300.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	10.0 in [25.4 cm]
Package Width	3.9 in [10.0 cm]
Package Height	1.7 in [4.3 cm]
Shipping (Package) Weight	10.7 oz [302.0 g]

---

**What's in the Box**

Included in Package	1 - NEMA 5-15P to C13 power cord
---------------------	----------------------------------

---

**Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

