

Cisco QSFP-40G-SR4 Compatible QSFP+ Module - 40GBASE-SR4 - 40GbE Multimode Fiber MMF Optic Transceiver - 40GE Gigabit Ethernet QSFP+ - MPO 150m - 850nm - DDM Cisco Firepower, ASR1000, ASR9000

**Product ID:** QSFP40GSR4ST



The QSFP40GSR4ST is a Cisco QSFP-40G-SR4 compatible fiber transceiver module that has been designed, programmed and tested to work with Cisco brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBASE-SR4 compliant networks, with a maximum distance of up to 150 m (492 ft).

**Technical Specifications:**

- Wavelength: 850nm
- Maximum Data Transfer Rate: 40 Gbps
- Type: Multi Mode Fiber
- Connection Type: MPO Connector
- Maximum Transfer Distance: 150 m (492 ft)
- MTBF: 1,649,326 hours
- Power Consumption: Less than 0.7 Watts
- Digital Diagnostics Monitoring (DDM): Yes

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

- Replacing defective or damaged SFP+ modules in Cisco switches and routers
- Expand your network to remote segments

## Features

- 100% CISCO QSFP-40G-SR4 COMPATIBLE: Works with Cisco switches like Firepower, ASR1000, ASR9000, C9300, C3850 and others
- TECHNICAL SPECS: 40GBASE-SR4 40 Gbps Multi Mode (MMF) MPO Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 150m (492ft)
- TESTED FOR OEM HOST COMPATIBILITY: Hot-swappable in Cisco routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- WORKS WITH MSA COMPLIANT SWITCHES: Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this SFP module is backed for life (lifetime of module, not network switch), including free lifetime 24/5 multi-lingual technical assistance.

---

### Hardware

Warranty	Lifetime
Compatible Brand	Cisco
Industry Standards	IEEE 802.3ba 40GBASE-SR4

---

### Performance

Maximum Data Transfer Rate	40 Gbps
Max Transfer Distance	150m [492ft]
Type	Multi Mode
Wavelength	850nm

---

Fiber Operating Mode	Full-Duplex
DDM	Yes
Compatible Networks	40 Gbps
MTBF	1,649,326 hours
Power Consumption (In Watts)	< 0.7 W

---

**Connector(s)**

Local Unit Connectors	1 - MPO
-----------------------	---------

---

**Special Notes / Requirements**

Note	For use in 40 Gigabit fiber networking equipment and media converters
------	---

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-40C to 85C (-40F to 185F)
Humidity	5~95% RH

---

**Physical Characteristics**

Color	Silver
Product Length	2.8 in [72.0 mm]
Product Width	0.7 in [1.8 cm]
Product Height	0.5 in [1.3 cm]
Weight of Product	1.1 oz [32.0 g]

---

**Packaging Information**

Package Length	4.6 in [11.6 cm]
Package Width	3.6 in [9.1 cm]
Package Height	1.3 in [3.4 cm]
Shipping (Package) Weight	2.0 oz [56.0 g]

**What's in the Box**

Included in Package	1 - QSFP+ transceiver
---------------------	-----------------------

---

**Warranty  
Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*

