

1.6ft (50cm) USB-C Fast Charging Cable, Rugged, Coiled, Charge & Sync, 3A, USB 2.0, TPE Jacket and Aramid Fiber - USB C Charging Cord

Product ID: R2CCC-50C-USB-CABLE



This 20in (50cm) coiled USB C cable can withstand the daily demands of charging and syncing your mobile devices. It contracts to 12in (32cm) making it compact and convenient to store.

The durable USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

The USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It supports up to 3A for charging your USB C compatible devices.

Certifications, Reports and Compatibility



Applications

Features

- **USB C CHARGING CABLE:** Coiling cable stretches up to 20in (50cm) and contracts to 12.5in (32cm) preventing it from being tangled; Strong but soft flexible TPE jacket, makes it easy to coil and put away in vehicle console or glove compartment

- **RUGGED DESIGN:** USB Type-C cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions & 5000+ bend cycles at 180 angle; Durable TPE jacket and strain relief; TPE is non-toxic, halogen free
- **FAST CHARGE AND SYNC :** Supporting up to 3A for fast charging from a USB-C port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices
- **USB-C COMPATIBILITY:** Heavy duty data transfer cable allows you to charge and sync your USB Type C devices including iPad Pro, Samsung Galaxy, One Plus, Google Pixel; (*Please note that USB 2.0 cables do not support video)
- **SPECS:** Length: 20in (50cm) Color: Black Connectors: USB-C to USB-C Performance: USB 2.0 Material: Aramid Fiber Power: 3A Jacket Type: TPE Shielding: EMI Protection

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Cable Length	19.7 in [500 mm]
Type and Rate	USB 2.0 - 480 Mbit/s

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Environmental

Operating Temperature	0 to 80C (32 to 176F)
Storage Temperature	0 to 80C (32 to 176F)
Humidity	0% to 95% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	22/32 AWG

Cable Length	1.6 ft [0.5 m]
Cable OD	0.1 in [3.1 mm]
Product Length	12.5 in [31.8 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.3 in [0.7 cm]
Weight of Product	1.0 oz [28.0 g]

Packaging Information

Package Quantity	1
Package Length	5.0 in [12.7 cm]
Package Width	5.0 in [12.6 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	1.2 oz [34.0 g]

What's in the Box

Included in Package	1 - USB-C to USB-C cable
---------------------	--------------------------

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

