

3ft (1m) Slim HDMI Cable, Flexible Premium Certified HDMI 2.0 Cord with Ethernet, UHD 4K 60Hz HDR10, Durable Aramid Fiber Design with TPE Jacket

Product ID: RHDMM1MP



This High Speed HDMI® Slim Cable with Ethernet withstands the daily demands of connecting your HDMI devices. Tested to endure strenuous wear and tear, the rugged cable is a must-have for both business and consumer applications.

Built for Daily Use

The Premium Certified Slim HDMI® 2.0 cable has aramid fiber reinforcement that braces it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

Cable Key Features

Aramid fiber adds strength and durability to the cable

Insulated conductors reduce friction, provide more flexibility

EMI protection with aluminum-mylar foil with braided shielding

TPE cable jacket is more flexible than a standard PVC cable

34AWG Slim HDMI cable with compact 4.7mm OD

Flexible Strain Relief

The cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.

Connector Key Features

HDMI gold plated connector with metal shield protects the circuit board from EMI and reinforces the connection point

Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

Supporting all HDMI 2.0 specifications, this HDMI® Premium Certified cable supports resolutions up to 4K 60Hz with a bandwidth of up to 18Gbps. The HDMI cable also supports HDR for higher contrast ratio and vivid colors providing an enriched and enjoyable viewing experience.

The terms HDMI, HDMI High-Definition Multimedia Interface, HDMI trade dress and the HDMI Logos are trademarks or registered trademarks of HDMI Licensing Administrator, Inc.

Certifications, Reports and Compatibility



Applications

- Connect 4K/Ultra HD displays and devices

Features

- **Premium Certified HDMI 2.0 with Ethernet**: HDMI cable supports 4K visuals and immersive audio, delivering 4K 60Hz (up to 4096x2160p), 18Gbps bandwidth, HDR10, ultra-wide aspect ratios, and 32-channel surround sound including Dolby Atmos and TrueHD
- **Ultra-durable materials**: HDMI cord with aramid fiber design provides extreme durability, increasing tensile strength so you can pull it through tight spaces and around extreme bends; Al-Mylar Foil with braid protects from EMI for reliable signal integrity
- **Navigate tight spaces with slim, flexible design**: TPE Jacket absorbs stress of frequent bends without damaging the cable; 34AWG Slim HDMI cable features a compact 4.7mm outer diameter for a clean, flexible fit in space-constrained environments
- **Connect across setups at home, work, or on the go**: Compatible with TVs, monitors, projectors, and soundbars; Works seamlessly with laptops, desktops, and streaming devices like Samsung, Sony, Dell, Apple TV, and more, HDMI 2.0 and previous HDMI versions
- **The IT Pro's Choice**: Our HDMI cables are rigorously tested in our Innovation Lab to ensure consistent signal integrity, durable construction, and broad compatibility across AV environments; Backed by free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Connector Plating	Gold
Cable Jacket Material	TPE - Thermoplastic Elastomers

	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance		
	Maximum Data Transfer Rate	18Gbps
	Audio Specifications	Up to 32 audio channels with 1536Hz sampling rate
Connector(s)		
	Connector A	1 - HDMI (19 pin)
		1 - HDMI (19 pin)
Physical Characteristics		
	Color	Black
	Connector Style	Straight
	Wire Gauge	34 AWG
	Cable Length	3.3 ft [1 m]
	Product Length	39.4 in [100.0 cm]
	Product Width	0.7 in [1.7 cm]
	Product Height	0.3 in [0.7 cm]
	Weight of Product	1.2 oz [33 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.1 in [20.7 cm]
	Package Width	5.9 in [15.1 cm]
	Package Height	0.9 in [2.2 cm]
	Shipping (Package) Weight	3.0 oz [84.0 g]
What's in the Box		
	Included in Package	1 - HDMI Cable

**Warranty
Information**

Warranty

Lifetime

****Product appearance and specifications are subject to change without notice.***