

12U 19" Desktop Open Frame Rack - 2 Post Free-Standing Network Rack Switch Depth for Patch Panel/Data/AV/Communication/Studio Equipment 110lb(50kg) Capacity w/Cage Nuts/Screws - TAA

Product ID: RK12OD



This 2-post desktop rack provides 12U of storage space for mounting smaller A/V and IT equipment.

With this 2-post rack, you can mount equipment at a fraction of the cost of conventional racks. The lightweight rack is engineered to meet EIA-310 rack-mount standards and is constructed of solid steel, ensuring a sturdy and safe mounting solution for your mission-critical equipment.

The rack features an open frame, free standing design that saves space with a small footprint. It gives you the ability to place rack-mount equipment on any surface in your office, such as your desk. This makes it easy to access your equipment on a daily basis.

The free standing network rack is easy to assemble and includes a pack of 20 M6 screws and cage nuts. If you're looking for other sizes, StarTech.com also offers 4U and 8U 2-post desktop computer racks.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The RK12OD is backed by a StarTech.com lifetime warranty and free technical support.

If you're looking for a desktop mounting solution with less rack units, StarTech.com also offers a 8U 2-post desktop rack and 4U 2-post desktop rack.

Certifications, Reports and Compatibility



Applications

- Mount patch panels, network switches, and routers in small or home office networks or IT offices to provide easy access to equipment
- Mount KVMs and rack-mount computer/server systems neatly on or beside your desk
- Mount AV equipment such as broadcast/distribution devices, switches or extenders

Features

- 2-POST 12U DESKTOP OPEN FRAME RACK: Ideal for use on a workbench or in the back room of small office spaces without dedicated wiring closets - offers easy access to IT equipment like switches or routers
- DESIGNED FOR EASY ACCESS: This free standing network rack is 12U in height with ample mounting space, and is ideal for environments where frequent front & rear access to equipment is required
- TECH SPECS: 12U Open Frame Rack; 19" Wide; 2 Post; EIA/ECA-310-E Compliant; U Heights Marked; 110lb (50 kg) Capacity; M6 Cage nuts & screws included
- EASY TO SHIP & SET UP: Quick and easy assembly combined w/6.8lb (3.1 kg) shipping weight makes the AV/studio switch depth rack ideal for remote sites - ships w/cage nuts & screws for mounting equipment
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this 2-Post 12U Desktop Open-Frame Rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	2-Post
Frame Type	Open Frame
U Height	12U
Special Features	Easy Assembly
	Easy Assembly
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)

Square (For Cage Nut)

Industry Standards EIA/ECA-310-E

EIA/ECA-310-E

Performance

Weight Capacity 110.2 lb [50 kg]

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 11.5 in [29.3 cm]

Product Width 19.8 in [50.3 cm]

Product Height 22.9 in [58.1 cm]

Weight of Product 5.6 lb [2.6 kg]

Maximum Mounting Depth 11.4 in [29.0 cm]

Packaging Information

Flat Pack (Assembly Required) Yes

Package Length 6.5 in [16.4 cm]

Package Width 24.1 in [61.1 cm]

Package Height 4.2 in [10.7 cm]

Shipping (Package) Weight 6.8 lb [3.1 kg]

What's in the Box

Included in Package 2 - 12U Vertical Post

2 - Legs

1 - Base Bracket

8 - Assembly Screws

20 - M5 Screws

20 - M5 Cage Nuts

4 - Rubber Feet

**Warranty
Information**

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*