


2-Post 12U Heavy-Duty Wall-Mount Network Rack, 19" Open Frame Server Rack, 12" Deep, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts & Screws Included

**Product ID:** RK12WALLO



This open-frame wall-mount server rack provides 12U of storage, allowing you to save space and stay organized. The equipment rack can hold up to 198 lb. (90 kg).

The network rack is 12 in. (30.5 cm) deep, so it's perfect for smaller spaces. It's easy to assemble and features mounting holes that are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing. The wall-mount rack comes in a flat-pack which makes it easy to transport and reduces shipping costs.

You can mount the open-frame rack where space is limited, such as on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

By having an open frame the server rack provides passive cooling to equipment. Additionally, the open frame provides easy access and configurability to your equipment, allowing you to maximize productivity.

The RK12WALLO is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location

- Mount audio/video broadcast or distribution components
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

## Features

- **2-POST 12U WALL MOUNT NETWORK RACK:** EIA/ECA-310 compliant open frame server rack with 11.9" (30.3cm) mounting depth is ideal for installing IT / AV / Data equipment, patch panels, switches and shelves in small spaces
- **HEAVY DUTY:** This heavy duty 2 post open frame rack supports unobstructed airflow and is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 200lbs (90Kg) of equipment
- **EFFICIENT FLAT PACK SHIPPING:** The IT rack ships flat packed with ISTA-6 certified packaging (assembly required) to ensure hassle-free installations with complete & undamaged delivery; Comprehensive assembly instructions included
- **HARDWARE INCLUDED:** The 2 post open frame wall mount server rack includes a complete set of M6 square cage nuts, M6 screws and washers to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 12U open frame wall mount rack is backed for 5 years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	12U
Special Features	Easy Assembly U-Markings Wall-Mountable
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

### Performance

Weight Capacity	198.4 lb [90 kg]
-----------------	------------------

---

**Physical Characteristics**

Color	Black
Construction Material	Steel

---

**Product Measurements**

Product Length	12.0 in [30.5 cm]
Product Width	19.8 in [50.4 cm]
Product Height	25.2 in [64.1 cm]
Weight of Product	19.1 lb [8.6 kg]
Maximum Mounting Depth	11.9 in [30.3 cm]

---

**Packaging Information**

Flat Pack (Assembly Required)	Yes
Package Length	21.2 in [53.8 cm]
Package Width	27.1 in [68.9 cm]
Package Height	5.4 in [13.8 cm]
Shipping (Package) Weight	24.2 lb [11.0 kg]

---

**What's in the Box**

Included in Package	48 - M6 Screws
	48 - M6 Cage Nuts
	48 - Washers
	16 - Assembly Screws
	2 - Vertical Rails
	2 - Horizontal Brackets
	1 - User Manual

---

**Warranty Information**

Warranty

5 Years

---

*\*Product appearance and specifications are subject to change without notice.*

