

## 4-Post 25U Server Rack Cabinet, Lockable 19" Data Rack Cabinet for Computer / AV / IT Equipment, Office / Home Network Rack with Casters & Adjustable Mounting Rails

**Product ID:** RK2537BKM



This 25U server rack provides a sleek, secure cabinet for storing standard 19" rack-mount devices such as Dell, HP, and IBM servers, along with telecommunication and A/V equipment. The rack is compatible with EIA-310 compliant equipment and supports a total load capacity of 1500 kg (3307 lb.).

This rack offers a variety of features that make it easy to install your equipment. With adjustable mounting rails, you can easily change the rail depth from 7 to 35 in. (76.2 mm - 939.8 mm) to support full-depth equipment. The added depth also provides support for additional cable and power management behind your equipment.

The rack features grommet holes on the ceiling and floor, which make it easy to run cabling in and out of the cabinet for discreet cable management. The rack also features grounding lugs that enable you to ground your equipment for added protection, and tool-less accessory mounting rails so you can mount 0U vertical cable managers and PDUs.

For hassle-free cable management, the rack includes a 3-meter roll of hook-and-loop cable tie that makes it easy to keep your cables tidy. You can cut the self-gripping fabric to any size, and bind your equipment cables together or to the rack.

To provide hassle-free deployment the rack ships fully assembled.

To keep your rack-mounted equipment secure, this rack features front and rear locking mesh doors that also increase airflow to provide passive cooling.

The rack also has a removable side panel with an independent quick-release lock that enables you to access your equipment easily, while still keeping it secure. Plus, a quick-release ceiling panel you can remove without interfering with cable runs that are running through your rack.

The cabinet features casters, providing ease of mobility around your office, studio or server room. Plus, the width and height of the rack fit through standard doorways, giving you the freedom to wheel your server rack into different rooms as needed.

The RK2537BKM is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Deploy in technology shops and repair centers that have limited space but tend to have mountable equipment that requires security
- Install rack-mount servers, KVM switches, networking equipment and cabinet consoles
- House rack-mount audio/video equipment for broadcasting in your editing room or television studio

## Features

- **ADJUSTABLE DEPTH:** 4- Post 25U 19" server rack enclosure with 4 vertical rails and adjustable mounting depth from 7.1" to 35.0" (18,0cm to 88,9cm); IT rack is compatible with various servers / switches / data / video / AV and other IT networking equipment
- **FULLY ASSEMBLED WITH CASTERS:** Enclosed 25U data rack cabinet ships pre-assembled with wheels & levelling feet to offer more stability; Home server rack cabinet is only 48.8in (123,9cm) in height, ideal for narrow home / office or server room spaces
- **DESIGN AND VENTILATION:** Half height server rack cabinet has lockable mesh doors and side panels with vented top allowing airflow; 4 Post 19" rack with 3307.5lb (1500kg) weight capacity (stationary); Computer cabinet rack is EIA/ECA-310-E Compliant
- **HARDWARE INCLUDED:** Rolling home network rack includes 50 M6 cage nuts and screws to mount equipment, 10 ft (3.1m) hook and loop fastener, 2x Door / Side Panels Keys and 1U Fixed Shelf; 1U height markings for easy positioning
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 25U IT Server Cabinet is backed for 5-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	5 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Enclosed Cabinet
U Height	25U

Special Features	Adjustable Mounting Rails
	Built-in Baying Tabs
	Built-in Cable Management
	Casters (Included)
	Grounding Lug(s)
	Leveling Feet
	Ships Fully Assembled
	U-Markings
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

---

#### Performance

Weight Capacity (Stationary)	3307.5 lb [1500 kg]
Weight Capacity for Racks (Rolling)	2315.2 lb [1050 kg]

---

#### Physical Characteristics

Color	Black
Front Door Construction	Steel Mesh
Front Door Features	Secure Key Lock with Reversible and Removable Front Door
Side Panel Construction	Steel
Side Panel Features	Secure Key Lock with Removable Side Panels
Rear Door Construction	Steel Mesh
Rear Door Features	Secure Key Lock with Removable Back Door

---

#### Product Measurements

Internal Width	23.7 in [60.1 cm]
----------------	-------------------

---

Internal Depth	42.3 in [107.4 cm]
Product Length	3.5 ft [1.1 m]
Product Width	23.6 in [60.0 cm]
Product Height	47.2 in [119.9 cm]
Weight of Product	180.4 lb [81.8 kg]
Maximum Mounting Depth	35.0 in [88.9 cm]
Minimum Mounting Depth	7.1 in [18 cm]
Product Height with Casters	48.8 in [123.9 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)	No
Package Length	3.8 ft [1.2 m]
Package Width	26.9 in [68.4 cm]
Package Height	4.5 ft [1.4 m]
Shipping (Package) Weight	251.4 lb [114.0 kg]

---

#### What's in the Box

Included in Package	1 - Server Rack Cabinet
	104 - M6 Cage Nuts
	104 - M6 Screws
	104 - Plastic Cup Washers
	2 - Keys
	1 - Hey Key
	1 - 10 ft. [3 m] Hook and Loop Tape
	1 - User Manual

---

#### Warranty Information

Warranty

5 Years

---

*\*Product appearance and specifications are subject to change without notice.*

